

HD10/12.FF5



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks
→ Railway Terminal Blocks

General Information

Extended Product Type:	HD10/12.FF5
Product ID:	1SNA295397R2600
EAN:	3472592953977
Catalog Description:	HD10/12.FF5 - Stud terminal blocks - 2 studs M5 - Beige
Long Description:	- 2 stud terminals M5 x 19.5 mm 0.768 in, - Equipment: H 130 self locking nut + TREP 3L washer + washer.

Ordering

Color:	Beige
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0205_CHD3
Instructions and Manuals:	1SNC160001C0205_CHD3

Dimensions

Product Net Width:	12 mm
Product Net Height:	50 mm
Product Net Depth / Length:	34.5 mm
Product Net Weight:	11 g

Technical

Rated Cross-Section:	10 mm ²
Spacing:	12 mm
Connection Type:	Stud
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Stud / Flexible 1x 0.5 ... 10 mm ²
Rated Current (I_n):	Main Circuit 57 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 1200 A
Rated Voltage (U_r):	750 V
Insulation Material:	Polyamide

Mounting on DIN Rail:	Type 2 (21.8 x 8.2 mm Mounting Rail) acc. to NFC 93461 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
------------------------------	--

Tightening Torque:	acc. IEC 60947-1 2.5 N·m
---------------------------	--------------------------

Technical UL/CSA

Connecting Capacity UL/CSA:	Stranded 8 AWG
------------------------------------	----------------

Flammability According to UL94:	V0
--	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225049U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220039E1002
Instructions and Manuals:	1SNC160001C0205_CHD3
RoHS Information:	1SND230014F0201

Classifications

Object Classification Code:	X
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	200 mm
Package Level 1 Depth / Length:	300 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.55 kg
Package Level 1 EAN:	3472592953977
Package Level 2 Units:	500 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 3 Units:	24000 piece
Product Packing Type:	Bag

