

# MC612PA 1->10 (x10) Horizontal



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Markers and Marking Systems  
→ Terminal Block Markers

## General Information

<b>Extended Product Type:</b>	MC612PA 1->10 (x10) Horizontal
<b>Product ID:</b>	1SNK150011R0000
<b>EAN:</b>	3472599999466
<b>Catalog Description:</b>	MC612PA Terminal Block Markers pre-printed : 1->10 (x10) Horizontal
<b>Long Description:</b>	MC612PA Terminal Block Markers pre-printed : 1->10 (x10) Horizontal White.

## Ordering

<b>Color:</b>	White
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	39269097

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK160007D0201
<b>Instructions and Manuals:</b>	1SNK160027C0201

## Dimensions

<b>Product Net Width:</b>	6 mm
<b>Product Net Height:</b>	12 mm
<b>Product Net Length:</b>	5.6 mm
<b>Product Net Depth / Length:</b>	5.6 mm
<b>Product Net Weight:</b>	11 g

## Technical

<b>Spacing:</b>	6 mm
<b>Function:</b>	Pre-printed marker card
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide

## Technical UL/CSA

<b>Flammability According to UL94:</b>	V2
--	----

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

**RoHS Status:**

Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

**Declaration of Conformity - CE:** 1SND225156C1000

**Environmental Information:** 1SND220060E1000

**Instructions and Manuals:** 1SNK160027C0201

**RoHS Information:** 1SND230504F0204

## Classifications

**Object Classification Code:** X

**E-number:** 2967593

**ETIM 4:** EC000761 - Labelling for terminal block

**ETIM 5:** EC000761 - Labelling for terminal block

**ETIM 6:** EC000761 - Labelling for terminal block

## Container Information

**Package Level 1 Units:** 1 piece

**Package Level 1 Width:** 120 mm

**Package Level 1 Depth / Length:** 200 mm

**Package Level 1 Gross Weight:** 0.011 kg

**Package Level 1 EAN:** 3472599999466

**Package Level 2 Units:** 600 piece

**Package Level 2 Gross Weight:** 6.6 kg

**Package Level 3 Units:** 14400 piece

