

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Protecting Covers

## General Information

<b>Extended Product Type:</b>	PL8
<b>Product ID:</b>	1SNK900620R0000
<b>EAN:</b>	3472599097513
<b>Catalog Description:</b>	PL8 Protecting Cover - Transparent
<b>Long Description:</b>	- Prohibit access to the screw clamps, - Indicate live circuits.

## Ordering

<b>Color:</b>	Transparent
---------------	-------------

<b>Minimum Order Quantity:</b>	10 piece
--------------------------------	----------

<b>Customs Tariff Number:</b>	39269097
-------------------------------	----------

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK160021D0201
---	-----------------

<b>Instructions and Manuals:</b>	1SNK160027C0201
----------------------------------	-----------------

## Dimensions

<b>Product Net Width:</b>	8 mm
---------------------------	------

<b>Product Net Height:</b>	49.2 mm
----------------------------	---------

<b>Product Net Length:</b>	25.05 mm
----------------------------	----------

<b>Product Net Depth / Length:</b>	25.1 mm
------------------------------------	---------

<b>Product Net Weight:</b>	2.6 g
----------------------------	-------

## Technical

<b>Spacing:</b>	8 mm
-----------------	------

<b>Function:</b>	Protecting Covers
------------------	-------------------

<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
------------------------------	--

<b>Insulation Material:</b>	Polycarbonate
-----------------------------	---------------

<b>Recommended Screw Driver:</b>	4 mm
----------------------------------	------

<b>Suitable For:</b>	ZS10
----------------------	------

## Technical UL/CSA

<b>Flammability According to UL94:</b>	V2
--	----

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	Compliant
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

<b>Instructions and Manuals:</b>	1SNK160027C0201
<b>RoHS Information:</b>	1SND230500F0202

## Classifications

<b>Object Classification Code:</b>	X
<b>E-nummer:</b>	2925168

## Container Information

<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	158 mm
<b>Package Level 1 Depth / Length:</b>	243 mm
<b>Package Level 1 Gross Weight:</b>	0.026 kg
<b>Package Level 1 EAN:</b>	3472599097513
<b>Package Level 2 Units:</b>	1500 piece
<b>Package Level 3 Units:</b>	72000 piece
<b>Product Packing Type:</b>	Bag

