

JB8-5-R1



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	JB8-5-R1
Product ID:	1SNK908905R0000
EAN:	3472599089051
Catalog Description:	JB8-5-R1 Jumper Bar - Orange
Long Description:	Insulated jumper bar with screw mounting.

Ordering

Color:	Orange
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

Dimensions

Product Net Width:	8 mm
Product Net Height:	40.5 mm
Product Net Length:	32.4 mm
Product Net Depth / Length:	32.4 mm
Product Net Weight:	19.4 g

Technical

Spacing:	8 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 50 A
Rated Voltage (U_r):	160 V
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Recommended Screw Driver:	3.5 mm
Suitable For:	ZS10-PE-R1 ZS10-R1 ZS10-ST

Technical UL/CSA

Flammability According to UL94:	V0
--	----

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230499F0203

Classifications

Object Classification Code: X

ETIM 4: EC000489 - Cross-connector for terminal block

ETIM 5: EC000489 - Cross-connector for terminal block

ETIM 6: EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units: 10 piece

Package Level 1 Width: 125 mm

Package Level 1 Depth / Length: 170 mm

Package Level 1 Height: 20 mm

Package Level 1 Gross Weight: 0.194 kg

Package Level 1 EAN: 3472599089051

Package Level 2 Units: 450 piece

Package Level 2 Width: 200 mm

Package Level 2 Depth / Length: 300 mm

Package Level 2 Height: 200 mm

Package Level 2 Gross Weight: 8.800 kg

Package Level 3 Units: 43200 piece

Product Packing Type: Bag

