



CABLE END CAPS CEC

SILICONE CABLE END CAPS FOR PROTECTION OF CABLE ENDS 0.6/1 kV

KEY FEATURES

- Reliable protection against humidity
- Tearproof, transparent silicon rubber
- Easy to install using lubricant
- Re-usable

TE Connectivity's (TE) silicone cable end caps are used to protect cable ends against humidity during transportation and outdoor storage. They have a high elasticity and toughness against crack propagation.

TE's cable end caps are also weatherproof and UV-resistant.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



PRODUCT SELECTION INFORMATION

Description	Cable Diameter [mm]	Application Range* [mm ²]	Pack Size	Part Number
GURO-CEC-8/12	8 - 12	3 - 4 x 1,5	10	CN1960-000
GURO-CEC-11/16	11 - 16	4 - 5 x 1,5 - 2,5	10	300158-000
GURO-CEC-16/22	16 - 22	4 - 5 x 4 - 16	10	890196-000
GURO-CEC-20/26	20 - 26	4 - 5 x 10 - 16 / 4 x 25	10	926542-000
GURO-CEC-23/30	23 - 30	4 - 5 x 25 - 35 / 4 x 50	10	096456-000
GURO-CEC-24/34	24 - 34	4 - 5 x 25 - 35 / 4 x 50	10	398064-000
GURO-CEC-30/38	30 - 38	4 x 50 - 70	10	548978-000
GURO-CEC-38/48	38 - 48	4 x 95 - 120	10	540908-000
GURO-CEC-44/54	44 - 54	4 x 120 - 185	10	625720-000

* Application Range should be seen as a guideline only, relevant specification is the cable diameter.

te.com/energy

©2014 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-1967-10/14

TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Benelux:	+ 32 16 351 731
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
China:	+ 86 (0) 400-820-6015