

General Information

Extended Product Type:	BAZH1
Product ID:	1SNK900102R0000
EAN:	3472599163690
Catalog Description:	BAZH1 End Stop - Dark Grey
Long Description:	- Give efficient support to the SNK double deck or power terminal blocks as assemblies thanks to the BAZH1 double gripping rail contact, - Ease the assemblies identification with label holders.

Ordering

Color:	Dark Grey
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK160026D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	10 mm
Product Net Height:	74.4 mm
Product Net Length:	30.2 mm
Product Net Depth / Length:	64.5 mm
Product Net Weight:	24 g

Technical

Spacing:	10 mm
Connection Type:	Screw clamp
Function:	End Stops
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Recommended Screw Driver:	5.5 mm

Suitable For: D35/16.PEN.2L
RGW25-M5
RGW25-M6
RGW6-R1
RGW6-ST-1
ZDK2.5-22
ZDK4-22
ZDP2.5-D1
ZDP2.5-D2
ZDS4-22
ZDS4-22-R1
ZK10
ZK10-3P
ZK10-PE
ZK10-PE-3P
ZK16
ZK16-3P
ZK16-PE
ZK16-PE-3P
ZK2.5
ZK2.5-3P
ZK2.5-4P
ZK2.5-CH-4P
ZK2.5-D1
ZK2.5-D1-PE
ZK2.5-D2
ZK2.5-D2-PE
ZK2.5-

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant

RoHS Status: Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

Environmental Information: 1SND220078E1000

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230479F0206

Classifications

Object Classification Code: X

E-number: 2925149

ETIM 4: EC001041 - End bracket for terminal block

ETIM 5: EC001041 - End bracket for terminal block

ETIM 6: EC001041 - End bracket for terminal block

Container Information

Package Level 1 Units: 20 piece

Package Level 1 Width: 225 mm

Package Level 1 Depth / Length: 320 mm

Package Level 1 Height: 5 mm

Package Level 1 Gross Weight: 0.48 kg

Package Level 1 EAN: 3472599163690

Package Level 2 Units: 360 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 400 mm

Package Level 2 Height: 200 mm

Package Level 3 Units: 17280 piece

Product Packing Type: Bag

