

K-TYPE™ CABLE MARKERS

Identification

TIE-ON PRE-PRINTED MARKERS FOR SIMPLE AND COST-EFFECTIVE IDENTIFICATION OF WIRES & CABLES

K-TYPE™ ‘Critchley’ Markers are designed to offer flexibility when it comes to wire and cable identification. Used to identify wire bundles, cables, pipes and conduits, the oval shaped profile has been designed to allow each marker to be accurately positioned onto a carrier strip and attached to the cable using cable ties. K-TYPE™ markers are ideal for post termination applications or where retrofitting is required.

SPEED-UP YOUR PROJECTS



- **Pre-Printed markers.** No Need for printers, ribbons and software. Pre-printing Markers allows easy and quick on-site installation.
- **Compact Design** to fit perfectly onto carrier strips allowing 1 to 18 markers to be installed. Attach the carrier strip to wire using common cable ties.
- **Easy identification** Kit available with pre-printed numbers, letters, common signs and carrier strips. Find and use the required markers quickly and easily.

SECURED INSTALLATION

- **Visual control:** Tie onto different substrate and wire size using common cable ties.
- **Strong & safe:** Made from Self-extinguishing plasticized PVC material.
- **Resistant to key Industrial fluids,** including those used in Mass transit, aviation and military.
- **Always perfect:** Elliptical marker profile allows easy fitting to carrier strips.
- **Extreme conditions:** Resist to temperature range from -45°C up to 70°C. Resistant to key industrial fluids, RoHS and REACH compliance.

FOR ALL YOUR NEEDS

- **Versatile marking:** Adapted to many substrates such as cables, cable bundles and conduit.
- **3 Carrier lengths:** Apply up to 7, 12 or 18 markers on the carrier to complete identification needs.
- **Large wire size range:** Choose your cable tie length.



K-Type™ cable markers

Identification & labelling

K-TYPE™ CABLE MARKERS

K-TYPE™ markers are ideal for post termination applications or where retrofitting is required.

K-TYPE™ markers are available in one size, designed to fit onto the carrier strips. The carrier strips are available in 3 sizes, holding from 1 to 18 markers and are made from plasticized PVC material.

Suitable for industrial applications.

Other colors available, consult your local TE Representative.

FEATURES

- Resistant to key industrial fluids, RoHS and REACH compliance
- Self-extinguishing plasticized PVC material
- Resistant to key Industrial fluids, including those used in Mass transit, aviation and military
- Versatile marking system for cables, cable bundles and conduit
- Elliptical marker profile allows easy fitting to carrier strips.

SPECIFICATIONS

- **Temperature rating:** operating range -45°C to 70°C (-49°F to 158°F)
- **Specifications and Approvals:** BS 6746C:1993 - IEC 60304
- **For more information:**
 - Technical Datasheet: TTDS-025
 - Product specification Sheet: RW-2535.

APPLICATIONS

- Industrial
- Electrical Cabinet
- Railway
- Oil & Gas.

ORDERING INFORMATION


LEGEND CODING		Letters					
Printed Marking Printed sign codification (legend)	A	B	C	D	E	F	
	10	11	12	13	14	15	
	G	H	I	J	K	L	
	16	17	18	19	20	21	
	M	N	O	P	Q	R	
	22	23	24	25	26	27	
	S	T	U	V	W	X	
	28	29	30	31	32	33	
	Y	Z					
	34	35					
	Numbers						
	0	1	2	3	4	5	
	00	01	02	03	04	05	
6	7	8	9				
06	07	08	09				
Sign							
+	-	/	⊥	.	BLANK		
PLUS	MINUS	SLASH	EARTH	DOT	BLANK		
36	37	38	40	48	49		

COLOR CODING

Only white & yellow are standard products.
Other colors on request.



ORDERING DESCRIPTION SYSTEM






K-Type™ cable markers

Identification & labelling

K-TYPE™ MARKERS SELECTION TABLE

- Tie on with cable Tie
- Marker height: 11.5 mm
- Marker Width: 6.0 mm
- Character Height: 4 mm

 Customized marking on request

Printed Character	Printed sign codification (Legend)					Packaging Qty (Pieces)	Packaging type
		TCPN	Part Description	TCPN	Part Description		
A	10	EC6529-000	13611910	EC6464-000	13611410	500	Reel
B	11	EC6530-000	13611911	EC6465-000	13611411		
C	12	EC6531-000	13611912	EC6466-000	13611412		
D	13	EC6532-000	13611913	EC6467-000	13611413		
E	14	EC6533-000	13611914	EC6468-000	13611414		
F	15	EC6534-000	13611915	EC6469-000	13611415		
G	16	EC6535-000	13611916	EC6470-000	13611416		
H	17	EC6536-000	13611917	EC6471-000	13611417		
I	18	EC6537-000	13611918	EC6472-000	13611418		
J	19	EC6538-000	13611919	EC6473-000	13611419		
K	20	EC6539-000	13611920	EC6474-000	13611420		
L	21	EC6540-000	13611921	EC6475-000	13611421		
M	22	EC6541-000	13611922	EC6476-000	13611422		
N	23	EC6542-000	13611923	EC6477-000	13611423		
O	24	EC6543-000	13611924	EC6478-000	13611424		
P	25	EC6544-000	13611925	EC6479-000	13611425		
Q	26	EC6545-000	13611926	EC6480-000	13611426		
R	27	EC6546-000	13611927	EC6481-000	13611427		
S	28	EC6547-000	13611928	EC6482-000	13611428		
T	29	EC6548-000	13611929	EC6483-000	13611429		
U	30	EC6549-000	13611930	EC6484-000	13611430		
V	31	EC6550-000	13611931	EC6485-000	13611431		
W	32	EC6551-000	13611932	EC6486-000	13611432		
X	33	EC6552-000	13611933	EC6487-000	13611433		
Y	34	EC6553-000	13611934	EC6488-000	13611434		
Z	35	EC6554-000	13611935	EC6489-000	13611435		
0	00	EC6519-000	13611900	EC6454-000	13611400		
1	01	EC6520-000	13611901	EC6455-000	13611401		
2	02	EC6521-000	13611902	EC6456-000	13611402		
3	03	EC6522-000	13611903	EC6457-000	13611403		
4	04	EC6523-000	13611904	EC6458-000	13611404		
5	05	EC6524-000	13611905	EC6459-000	13611405		
6	06	EC6525-000	13611906	EC6460-000	13611406		
7	07	EC6526-000	13611907	EC6461-000	13611407		
8	08	EC6527-000	13611908	EC6462-000	13611408		
9	09	EC6528-000	13611909	EC6463-000	13611409		
+	36	EC6555-000	13611936	EC6490-000	13611436		
-	37	EC6556-000	13611937	EC6491-000	13611437		
/	38	EC6557-000	13611938	EC6492-000	13611438		
i	40	EC6559-000	13611940	EC6494-000	13611440		
.	48	EC6564-000	13611948	EC6401-000	13611448		

K-Type™ cable markers

Identification & labelling

K-TYPE™ MARKERS KIT


- Marker kit contain 100 markers of legend: 0-9, A-Z, +, -, /, earth, Dot, and Blank markers, 4200 pieces in total. Also within the kits are 100 pieces of the 7 Digit Carrier Strip and 200 pieces of the 12 Digit Carrier Strip.

Marker Qty	Color	TCPN	Part Description	Packaging Qty (Kit)	Packaging type
4200	Yellow	EC9759-000	CCK-ERK-3-B/Y	1	Box
4200	White	CY2995-000	CCK-ERK-3-B	1	Box



K-TYPE™ MARKERS CARRIERS

Max Qty of Markers Per Carrier	Color	TCPN	Part Description	Packaging Qty (Pieces)	Packaging type
7	Black	EC4943-000	11320000	500	Bag
12	Black	EC4942-000	11310000	500	Bag
18	Black	EC4941-000	11300000	200	Bag



Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need.

Visit www.te.com/support to chat with a Product Information Specialist.

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2021 TE Connectivity. All Rights Reserved.

ELECTRICAL / K-TYPE™ CABLE MARKERS / BROCHURE / EN

09/21

PRODUCT SHEET

TE Connectivity
3, rue Jean Perrin
69687 Chassieu cedex
France
Tel: +33 481923100