

# MINING REPAIR SLEEVE (MRSM/MRS) 2 kV, HEAT-SHRINK, WRAPAROUND, FLAME RETARDANT

## **KEY FEATURES**

- Easy to use
- Flexible
- MSHA approved

TE Connectivity's (TE) Raychem MRSM/MRS repair sleeves provide an efficient method of repairing insulation on flexible cables up to 2 kV, and also helps in repairing damaged jackets on High Voltage cables where a splice is not required.

The MRSM/MRS is specially formulated to be flame retardant and its flexible wraparound sleeve installs easily to restore and repair trailing cables.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.







PRODUCT SELECTION INFORMATION: INCHES (mm)				
Description	Cable Use Range (min - max)	Sleeve Length	Standard Pack (pcs./Box)	
MRS-12-10	1.00 - 1.60 (25 - 41)	10 (254)	20	
MRS-12-24	1.00 - 1.60 (25 - 41)	24 (610)	10	
MRS-34-24	1.60 - 2.30 (41 - 58)	24 (610)	10	
MRS-34-30	1.60-2.30 (41 - 58)	30 (762)	10	
MRS-56-30	2.30 - 3.50 (58 - 89)	30 (762)	10	

Dimension values provided are typical.

REFERENCE DIMENSIONS FOR FEILD CUTTING OF CRSM: INCHES (mm)		
Damage Length	Total Seal Length	
<3 (<76)	3 (76)	
3 - 12 (76 - 305)	4 (102)	
12 - 24 (305 - 610)	6 (152)	
> 24 (>610)	8 (203)	

# ORDERING INFORMATION

Kit includes wrap around sleeve and stainless steel channel closure

Kit does not contain connectors.

Bulk options are also available. Consult your TE Connectivity representative.

## **TECHNICAL REPORT**

Related test reports: EDR-5028

### te.com/energy

©2014 TE Connectivity Ltd. family of companies. All Rights Reserved. E565 10/2014

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

#### FOR MORE INFORMATION: TE Technical Support Centers

USA:
France:
UK:
Germany:
Spain:
Benelux:
Canada:
Mexico:
Latin/S. America:
China:

+ 1 800 327 6996 + 33 380 583 200 + 44 0870 870 7500 + 49 896 089 903 + 34 916 630 400 + 32 16 351 731 + 1 (905) 475-6222 + 52 (0) 55-1106-0800 + 54 (0) 11-4733-2200

+ 86 (0) 400-820-6015

