

AMP-TY

TE Internal #: 2-100694-1


Cable Tie Mounts & Accessories, Cable Tie Mount, 2-Way Professional, Adhesive Back, .169in [4.3mm] Cable Tie Mount &

Accessory Width, Polyamide 6.6 GF

View on TE.com >



Wire & Cable > Wire & Cable Accessories > Cable Tie Mounts & Accessories



Cable Tie Mount Accessory Type: Cable Tie Mount

Cable Tie Mount & Accessory Mounting Type: 2-Way Professional

Adhesive Back: With

Cable Tie Mount & Accessory Width: 4.3 mm [.169 in]
Cable Tie Mount & Accessory Material: Polyamide 6.6 GF

Features

Product Type Features

Product Type	Accessory
Cable Tie Mount Accessory Type	Cable Tie Mount
Body Features	
Cable Tie Mount & Accessory Material	Polyamide 6.6 GF
Cable Tie Mount & Accessory Color	Natural
Mechanical Attachment	
Cable Tie Mount & Accessory Mounting Type	2-Way Professional
Adhesive Back	With
Dimensions	
Overall Outside Diameter	4.3 mm[.169 in]
Cable Tie Mount & Accessory Width	4.3 mm[.169 in]
Packaging Features	
Cable Tie Mount & Accessory Packaging Method	Box & Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



Customers Also Bought









Cable Tie Mounts & Accessories, Cable Tie Mount, 2-Way Professional, Adhesive Back, .169in [4.3mm] Cable Tie Mount & Accessory Width, Polyamide 6.6 GF





Documents

Product Drawings
MOUNTING BASE,NAT.

English