

AMP-TY

TE Internal #: 2-106093-2

Cable Tie Mounts & Accessories, Cable Tie Mount, Screw,
Adhesive Back, .354in [9mm] Cable Tie Mount & Accessory Width,
Polyamide 6.6 GF, Black

[View on TE.com >](#)

Wire & Cable > Wire & Cable Accessories > Cable Tie Mounts & Accessories

Cable Tie Mount Accessory Type: **Cable Tie Mount**Cable Tie Mount & Accessory Mounting Type: **Screw**Adhesive Back: **With**Cable Tie Mount & Accessory Width: **9 mm [.354 in]**Cable Tie Mount & Accessory Material: **Polyamide 6.6 GF****Features****Product Type Features**

Product Type	Accessory
Cable Tie Mount Accessory Type	Cable Tie Mount

Body Features

Cable Tie Mount & Accessory Material	Polyamide 6.6 GF
Cable Tie Mount & Accessory Color	Black

Mechanical Attachment

Cable Tie Mount & Accessory Mounting Type	Screw
Adhesive Back	With

Dimensions

Overall Outside Diameter	9 mm [.354 in]
Cable Tie Mount & Accessory Width	9 mm [.354 in]

Packaging Features

Cable Tie Mount & Accessory Packaging Method	Box & Carton
--	--------------

Product Compliance[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 608803-1 CABLE TIE MOUNT, 4-WAY, 1-1/8"</p>	 <p>TE Part # 608802-1 CABLE TIE MOUNT, 4-WAY, 3/4"</p>	 <p>TE Part # 608801-1 CABLE TIE MOUNT, 2-WAY</p>	 <p>TE Part # 607847-1 CABLE TIE MOUNT</p>
--	---	--	---

Customers Also Bought

 <p>TE Part #62734-2 SHPL REC IS 18-14 .018SPBR</p>	 <p>TE Part #163083-8 .062 DIA SOC.ASS.3+</p>	 <p>TE Part #4-160971-2 CABLE TY 140X3.6 BLACK</p>	 <p>TE Part #5575754001 Single Wall CGPT Spool Heat Shrink Tubin</p>
--	---	---	---

