




ENTRELEC

Electrical Solutions



CABLE-TIE-ON PRE-PRINTED MARKERS

Wire and cable identification
applied using cable ties

The ENTRELEC Cable-Tie-On Markers are designed to offer flexibility with wire and cable identification. Each marker is designed to be accurately positioned onto a carrier strip and attached to the substrate using cable ties, this provides compatibility with multiple wire sizes. Made from Self-extinguishing PVC these are a cost-effective solution for many identification applications.



SPEED UP YOUR PROJECTS

Pre-Printed

No need for printers, ribbons and software. Markers are Pre-printed for easy and quick application.

Compact design

Fit perfectly onto carrier strip allowing 1 – 18 markers to be installed. Tie carrier strip to wire using common cable tie.

Easy identification

Kit available with pre-printed numbers, letters, pre-printed numbers, letters, common signs and carrier strips. Find and use the required marker quickly and easily.



EASY TO INSTALL

Visual control

Tie onto different wire sizes using cable ties.

Strong and safe

Made from Self-extinguishing plasticized PVC material.

Always perfect

Elliptical marker profile allows easy and accurate fitting to carrier strips.



FOR ALL YOUR NEEDS

3 carrier lengths

Apply up to 7, 12, or 18 markers on the carrier to complete identification needs

Large wire size range

Choose your cable tie length as required for wire or cable bundle diameter.


Extreme conditions

Resist to an ambient temperature range from -45°C to 70°C.


Resistant to key Industrial fluid. RoHS and REACH compliance.



ORDERING DESCRIPTION SYSTEM



MOUNTING INSTRUCTIONS



PRODUCT ORDERING INFORMATION



Black Carrier strip for markers

- Carrier length: 66/97/134 mm
- Carrier height: 9.5 mm
- Packing: 500 & 250 per bags

| Description | Part Number |
|--------------------|-----------------|
| CTO-Carrier-500-7 | 1SET512170R0000 |
| CTO-Carrier-500-12 | 1SET512171R0000 |
| CTO-Carrier-250-18 | 1SET512172R0000 |



Markers kit

- Characters: A-Z, 0-9 symbols +, -, /, earth, Dot, Blank
- Character total quantity: 4200 pieces (42 types of characters x 100)



White color / Printed black

| Description | Part Number |
|-----------------|-----------------|
| CTO-Kit-4200-WH | 1SET512000R0000 |



Yellow color / Printed black


| Description | Part Number |
|-----------------|-----------------|
| CTO-Kit-4200-YL | 1SET512001R0000 |



CABLE-TIE-ON PRE-PRINTED MARKERS



- L (Marker Width): 6 mm
- H (Character Height): 4 mm
- Packing: 100 per bags



White color / Printed black



Yellow color / Printed black

| Printed Character | Description | Part Number | | Description | Part Number |
|-------------------|-----------------------------|-----------------|--|-----------------------------|-----------------|
| A | CTO-Marker-0-100-A-WH | 1SET512012R0000 | | CTO-Marker-0-100-A-YL | 1SET512096R0000 |
| B | CTO-Marker-0-100-B-WH | 1SET512013R0000 | | CTO-Marker-0-100-B-YL | 1SET512097R0000 |
| C | CTO-Marker-0-100-C-WH | 1SET512014R0000 | | CTO-Marker-0-100-C-YL | 1SET512098R0000 |
| D | CTO-Marker-0-100-D-WH | 1SET512015R0000 | | CTO-Marker-0-100-D-YL | 1SET512099R0000 |
| E | CTO-Marker-0-100-E-WH | 1SET512016R0000 | | CTO-Marker-0-100-E-YL | 1SET512100R0000 |
| F | CTO-Marker-0-100-F-WH | 1SET512017R0000 | | CTO-Marker-0-100-F-YL | 1SET512101R0000 |
| G | CTO-Marker-0-100-G-WH | 1SET512018R0000 | | CTO-Marker-0-100-G-YL | 1SET512102R0000 |
| H | CTO-Marker-0-100-H-WH | 1SET512019R0000 | | CTO-Marker-0-100-H-YL | 1SET512103R0000 |
| I | CTO-Marker-0-100-I-WH | 1SET512020R0000 | | CTO-Marker-0-100-I-YL | 1SET512104R0000 |
| J | CTO-Marker-0-100-J-WH | 1SET512021R0000 | | CTO-Marker-0-100-J-YL | 1SET512105R0000 |
| K | CTO-Marker-0-100-K-WH | 1SET512022R0000 | | CTO-Marker-0-100-K-YL | 1SET512106R0000 |
| L | CTO-Marker-0-100-L-WH | 1SET512023R0000 | | CTO-Marker-0-100-L-YL | 1SET512107R0000 |
| M | CTO-Marker-0-100-M-WH | 1SET512024R0000 | | CTO-Marker-0-100-M-YL | 1SET512108R0000 |
| N | CTO-Marker-0-100-N-WH | 1SET512025R0000 | | CTO-Marker-0-100-N-YL | 1SET512109R0000 |
| O | CTO-Marker-0-100-O-WH | 1SET512026R0000 | | CTO-Marker-0-100-O-YL | 1SET512110R0000 |
| P | CTO-Marker-0-100-P-WH | 1SET512027R0000 | | CTO-Marker-0-100-P-YL | 1SET512111R0000 |
| Q | CTO-Marker-0-100-Q-WH | 1SET512028R0000 | | CTO-Marker-0-100-Q-YL | 1SET512112R0000 |
| R | CTO-Marker-0-100-R-WH | 1SET512029R0000 | | CTO-Marker-0-100-R-YL | 1SET512113R0000 |
| S | CTO-Marker-0-100-S-WH | 1SET512030R0000 | | CTO-Marker-0-100-S-YL | 1SET512114R0000 |
| T | CTO-Marker-0-100-T-WH | 1SET512031R0000 | | CTO-Marker-0-100-T-YL | 1SET512115R0000 |
| U | CTO-Marker-0-100-U-WH | 1SET512032R0000 | | CTO-Marker-0-100-U-YL | 1SET512116R0000 |
| V | CTO-Marker-0-100-V-WH | 1SET512033R0000 | | CTO-Marker-0-100-V-YL | 1SET512117R0000 |
| W | CTO-Marker-0-100-W-WH | 1SET512034R0000 | | CTO-Marker-0-100-W-YL | 1SET512118R0000 |
| X | CTO-Marker-0-100-X-WH | 1SET512035R0000 | | CTO-Marker-0-100-X-YL | 1SET512119R0000 |
| Y | CTO-Marker-0-100-Y-WH | 1SET512036R0000 | | CTO-Marker-0-100-Y-YL | 1SET512120R0000 |
| Z | CTO-Marker-0-100-Z-WH | 1SET512037R0000 | | CTO-Marker-0-100-Z-YL | 1SET512121R0000 |
| + | CTO-Marker-0-100-(PLS)-WH | 1SET512038R0000 | | CTO-Marker-0-100-(PLS)-YL | 1SET512122R0000 |
| - | CTO-Marker-0-100-(MIN)-WH | 1SET512039R0000 | | CTO-Marker-0-100-(MIN)-YL | 1SET512123R0000 |
| / | CTO-Marker-0-100-(SLH)-WH | 1SET512040R0000 | | CTO-Marker-0-100-(SLH)-YL | 1SET512124R0000 |
| ⚡ | CTO-Marker-0-100-(ETH)-WH | 1SET512041R0000 | | CTO-Marker-0-100-(ETH)-YL | 1SET512125R0000 |
| . | CTO-Marker-0-100-(DOT)-WH | 1SET512042R0000 | | CTO-Marker-0-100-(DOT)-YL | 1SET512126R0000 |
| | CTO-Marker-0-100-(blank)-WH | 1SET512043R0000 | | CTO-Marker-0-100-(blank)-YL | 1SET512127R0000 |
| 0 | CTO-Marker-0-100-0-WH | 1SET512002R0000 | | CTO-Marker-0-100-0-YL | 1SET512086R0000 |
| 1 | CTO-Marker-0-100-1-WH | 1SET512003R0000 | | CTO-Marker-0-100-1-YL | 1SET512087R0000 |
| 2 | CTO-Marker-0-100-2-WH | 1SET512004R0000 | | CTO-Marker-0-100-2-YL | 1SET512088R0000 |
| 3 | CTO-Marker-0-100-3-WH | 1SET512005R0000 | | CTO-Marker-0-100-3-YL | 1SET512089R0000 |
| 4 | CTO-Marker-0-100-4-WH | 1SET512006R0000 | | CTO-Marker-0-100-4-YL | 1SET512090R0000 |
| 5 | CTO-Marker-0-100-5-WH | 1SET512007R0000 | | CTO-Marker-0-100-5-YL | 1SET512091R0000 |
| 6 | CTO-Marker-0-100-6-WH | 1SET512008R0000 | | CTO-Marker-0-100-6-YL | 1SET512092R0000 |
| 7 | CTO-Marker-0-100-7-WH | 1SET512009R0000 | | CTO-Marker-0-100-7-YL | 1SET512093R0000 |
| 8 | CTO-Marker-0-100-8-WH | 1SET512010R0000 | | CTO-Marker-0-100-8-YL | 1SET512094R0000 |
| 9 | CTO-Marker-0-100-9-WH | 1SET512011R0000 | | CTO-Marker-0-100-9-YL | 1SET512095R0000 |

te.com

ENTRELEC, TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2021 TE Connectivity Ltd. family of companies All Rights Reserved.

INDUSTRIAL / ENTRELEC CABLE-TIE-ON PRE-PRINTED MARKERS / BROCHURE / EN

08/21

PRODUCT SHEET

TE Connectivity
3, rue Jean Perrin
69687 Chassieu cedex
France
Tel: +33 481923100