

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Circuit Separators

General Information

Extended Product Type:	CS-R2
Product ID:	1SNK900106R0000
EAN:	3472599857698
Catalog Description:	CS-R2 Circuit Separator - Dark Grey
Long Description:	- Compact circuits separator solution (only 3mm spacing) which provides a convenient visual identification of the several circuits within terminal assemblies, - Unique top marking possibility that can replace the conventional solution of "end stop with label holder" for demanding applications with high space constraints, - Compatible with all PI-spring feed-through and ground terminal blocks up to 8 mm spacing, - Mounting on DIN3-TH35 rail.

Ordering

Color:	Dark Grey
Minimum Order Quantity:	20 piece
Customs Tariff Number:	39269097

Popular Downloads

Data Sheet, Technical Information:	1SNK160027C0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	3 mm
Product Net Height:	61.8 mm
Product Net Depth / Length:	48.7 mm
Product Net Weight:	3.8 g

Technical

Spacing:	3 mm
Function:	Circuit Separators
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Suitable For: ZK2.5
ZK2.5-PE
ZK4
ZK4-PE
ZK6
ZK6-PE

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

RoHS Status: Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230535F0201

Classifications

Object Classification Code: X

ETIM 4: EC000897 - Feed-through terminal block

ETIM 5: EC000897 - Feed-through terminal block

ETIM 6: EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units: 20 piece

Package Level 1 Width: 155 mm

Package Level 1 Depth / Length: 200 mm

Package Level 1 Height: 10 mm

Package Level 1 Gross Weight: 0.097 kg

Package Level 1 EAN: 3472599857698

Package Level 2 Units: 1000 piece

Package Level 2 Width: 400 mm

Package Level 2 Depth / Length: 600 mm

Package Level 2 Height: 250 mm

Package Level 3 Units: 40000 piece

Product Packing Type: Bag

