

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Protecting Covers

General Information

Extended Product Type:	PL6
Product ID:	1SNK900619R0000
EAN:	3472599097506
Catalog Description:	PL6 Protecting Cover - Transparent
Long Description:	- Prohibit access to the screw clamps, - Indicate live circuits.

Ordering

Color:	Transparent
---------------	-------------

Minimum Order Quantity:	10 piece
--------------------------------	----------

Customs Tariff Number:	39269097
-------------------------------	----------

Popular Downloads

Data Sheet, Technical Information:	1SNK160021D0201
---	-----------------

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

Dimensions

Product Net Width:	6 mm
---------------------------	------

Product Net Height:	49.2 mm
----------------------------	---------

Product Net Length:	25.05 mm
----------------------------	----------

Product Net Depth / Length:	25.1 mm
------------------------------------	---------

Product Net Weight:	1.8 g
----------------------------	-------

Technical

Spacing:	6 mm
-----------------	------

Function:	Protecting Covers
------------------	-------------------

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
------------------------------	--

Insulation Material:	Polycarbonate
-----------------------------	---------------

Recommended Screw Driver:	4 mm
----------------------------------	------

Suitable For:	ZS6 ZS6-S
----------------------	--------------

Technical UL/CSA

Flammability According to UL94:	V2
--	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
--	-----------

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

RoHS Information:	1SND230500F0202
--------------------------	-----------------

Classifications

Object Classification Code:	X
------------------------------------	---

E-nummer:	2925167
------------------	---------

Container Information

Package Level 1 Units:	10 piece
-------------------------------	----------

Package Level 1 Width:	158 mm
-------------------------------	--------

Package Level 1 Depth / Length:	243 mm
--	--------

Package Level 1 Gross Weight:	0.018 kg
--------------------------------------	----------

Package Level 1 EAN:	3472599097506
-----------------------------	---------------

Package Level 2 Units:	1500 piece
-------------------------------	------------

Package Level 3 Units:	72000 piece
-------------------------------	-------------

Product Packing Type:	Bag
------------------------------	-----

