



2 B2	PART NUMBER	PLATING PIN BODY	PLATING HOOD
	38941-22/38941-20 38941-16/38941-12	.000050 MIN. GOLD PER MIL-G-45204 OVER NICKEL	PASSIVATED
	38941-22L/38941-20L 38941-16L/38941-12L	SELECTIVE PLATING PER MIL-C-39029	PASSIVATED

REV	38941-**
B	

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
A	REVISED PER E.O. C2942	97-10-20	BJH
B	REVISED PER E.O. C6219	050331	gpc




DETAIL Z
SIZE 22D ONLY

DEUTSCH PART NO.	MILITARY PART NO.	COLOR BANDS			SIZE	WIRE GAGE RANGE	RECOMMENDED STRIP LENGTH	CRIMP TOOL				A MIN.	B MIN.	C MAX.
		1ST	2ND	3RD				DEUTSCH TOOL	POSITIONER	NS TOOL	POSITIONER			
38941-22 38941-22L	MIL-C-39029/58-360	ORANGE	BLUE	BLACK	22D	22, 24, 26, 28	.160 TO .190	M15500-222016-1	15600-3622	M22520/2-01	M22520/2-09	.141	.0335	.048
38941-20 38941-20L	MIL-C-39029/58-363	ORANGE	BLUE	ORANGE	20	20, 22, 24	.230 TO .260	M15500-222016-1	15600-3520	M22520/7-01	M22520/7-07	.209	.046	.070
38941-16 38941-16L	MIL-C-39029/58-364	ORANGE	BLUE	YELLOW	16	16, 18, 20	.230 TO .260	M15500-222016-1	15600-3616	M22520/1-01	M22520/1-04	.209	.066	.103
38941-12 38941-12L	MIL-C-39029/58-365	ORANGE	BLUE	GREEN	12	12 AND 14	.230 TO .260			M22520/7-01	M22520/7-04	.209	.098	.151

- 3. MATERIALS: PIN-COPPER ALLOY.
- 2. FINISH: SEE TABLE A (B1)
- 1. DIMENSIONS ARE INCHES UNLESS OTHERWISE SPECIFIED.

NOTES: UNLESS OTHERWISE SPECIFIED.

TOLERANCE UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
DECIMALS .XXX ± .005; .XXXX ± .0005
ANGLES: X° ± .5°; X.X° ± .25°
T.I.R. .010
PARTS TO BE FREE OF BURRS & SHARP EDGES



ALL SHEETS ARE THE SAME REVISION STATUS
PROPERTY OF DEUTSCH E.C.D.
THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT SHALL NOT BE DISCLOSED, DUPLICATED,
NOR USED IN WHOLE OR IN PART FOR ANY PURPOSE OTHER THAN TO EVALUATE THIS DRAWING

SIGNATURE & DATE		DEUTSCH DEFENSE/AEROSPACE OPERATION 5733 WEST WHITTIER AVE. HEMET, CA 92545	
DR	C. GAREN 05-02-24	TITLE	CONACT, PIN CRIMP TYPE MIL-C-39029/58 ENVELOPE
CHK	gpc 050331	SIZE	B
PE	C. GAREN 05-02-24	CAGE CODE	11139
APPD	[Signature]	DWG NO	38941-**
MATERIAL		SCALE	NONE
FINISH		WEIGHT	
MATERIAL CODE		SHEET	1 OF 1