

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2016

© COPYRIGHT 2015

BY TE CONNECTIVITY

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-16-001116	27JAN2016	JA	DM
	A1	REVISED PER ECO-16-003159	03MAR2016	JA	DM

1.000
[25.40]

2

DT04-08P

5

4

6

9

7

8

DEUTSCH

DEUTSCH-USA

6

1.848
[46.94]

5

1.435
[36.45]

7. SEE SHEET 2 FOR ALL KEY ARRANGEMENTS.

6

BORDER SIGNIFIES THAT PINS 7 AND 8 ARE BUSSED TOGETHER, PINS 5 AND 6 ARE BUSSED TOGETHER, AND PINS 3 AND 4 ARE BUSSED TOGETHER WITH A TWO PIN BUSSBAR. CAVITIES 1 AND 2 ARE NOT USED.

5

DATE CODE; YEAR IS REPRESENTED BY THE LAST NUMERICAL DIGIT, EX: 0 = 2010. MONTH IS REPRESENTED BY SEQUENTIAL ALPHA CHARACTERS, EX: A = JANUARY.

4

MATERIAL - RECEPTACLE: PA66 GF15 (SEE COLOR TABLE) WEDGE LOCK (INCLUDED): PBT GF30 (GREEN) BUSSBARS: COPPER ALLOY, NICKEL PLATED

3. EACH 2 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 13 AMPS.

2

ORIENTATION OF "DEUTSCH" AND "-P089" TO BE OPTIONAL.

1. MATES WITH DT06-08SX-XXXX (X = KEY A,B,C,D) (XXXX = ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCH [mm]

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±.025 [0.63]

4 PLC ±

ANGLES ±0° 30' 0"

FINISH

MATERIAL

4

TOLERANCES UNLESS OTHERWISE SPECIFIED:

03DEC2015
R. MESSENGER

26JAN2016
DENNIS WHITACRE

26JAN2016
DAVID MEYER

PRODUCT SPEC
108-151009

APPLICATION SPEC
0425-017-00000

WEIGHT
23.71g

CUSTOMER DRAWING

TE

TE Connectivity

NAME
8 PIN RECEPTACLE, (3) 2 PIN BUSSBARS
DT SERIES

SIZE
A3

CAGE CODE
4AFU8

DRAWING NO
DT04-08PX-P089

RESTRICTED TO
-

SCALE
2:1

SHEET
1 OF 2

REV
A1

1470-19 (3/13)

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2016

© COPYRIGHT 2015

BY TE CONNECTIVITY

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

KEY A

KEY B

KEY C

KEY D

DT04-08PA-P089

COLOR: GREY

DT04-08PB-P089

COLOR: BLACK

DT04-08PC-P089

COLOR: GREEN

DT04-08PD-P089

COLOR: BROWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

INCH [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±.025 [0.63]

4 PLC ±

ANGLES ±0° 30' 0"

FINISH

MATERIAL

4

DWN 03DEC2015

R. MESSENGER

CHK 26JAN2016

DENNIS WHITACRE

APVD 26JAN2016

DAVID MEYER

PRODUCT SPEC

108-151009

APPLICATION SPEC

0425-017-00000

WEIGHT

23.71g

CUSTOMER DRAWING

TE Connectivity

NAME

8 PIN RECEPTACLE, (3) 2 PIN BUSSBARS

DT SERIES

SIZE

A3

CAGE CODE

4AFU8

DRAWING NO

DT04-08PX-P089

RESTRICTED TO

-

SCALE

1:1

SHEET

2

OF

2

REV

A1

1470-19 (3/13)