



| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|---------------|-----------|-----|------|
| | B | ECR-20-003872 | 24FEB2020 | GK | MN |

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]

TE PN: E81542-000

**OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 2000**

| | |
|---------------|-----------------|
| MATERIAL | WHITE POLYESTER |
| ADHESIVE TYPE | PERMANENT |
| LINER | GLASSINE PAPER |

| TOLERANCES mm [INCH] | |
|----------------------|--------------|
| LABEL HEIGHT: | ±0.3 [.012] |
| LABEL WIDTH: | ±0.3 [.012] |
| WEB WIDTH: | ±0.8 [.031] |
| VERTICAL REPEAT: | ±0.8 [.031]* |
| HORIZONTAL REPEAT: | ±0.8 [.031]* |
| PRINT POSITIONING: | ±0.8 [.031]* |
| LEFT MARGIN: | ±0.4 [.016] |
| QUANTITY: | -0 % +2 % |
| *NON ACCUMULATING | |

| | |
|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | |
| DIMENSIONS: mm [INCHES] | TOLERANCES UNLESS OTHERWISE SPECIFIED: |
| | 0 PLC ± - |
| | 1 PLC ± - |
| | 2 PLC ± - |
| | 3 PLC ± - |
| | 4 PLC ± - |
| ANGLES ± - | FINISH - |
| MATERIAL SEE TABLE | |

| | |
|------------------|-----------|
| DWN | 02AUG2006 |
| GOPALAKRISHNA HV | |
| CHK | 02AUG2006 |
| K. MUNZ | |
| APVD | 02AUG2006 |
| K. MUNZ | |
| PRODUCT SPEC | |
| TTDS-073 | |
| APPLICATION SPEC | |
| WEIGHT | 0.178g |

| | | | | |
|------------------|-----------|-----------------------------|--------|---------------|
| TE Connectivity | | NAME | | RESTRICTED TO |
| | | WP - WHITE POLYESTER LABELS | | |
| SIZE | CAGE CODE | DRAWING NO | - | |
| A3 | C2290 | G-WP-445445-2-9 | - | |
| CUSTOMER DRAWING | | SCALE | SHEET | REV |
| | | NTS | 1 OF 1 | B |