

TE Connectivity Products *FIRST*® Robotics Competition

TE Connectivity's products are a crucial part of an increasingly connected world. We can sense and connect data, power or signals moving through just about anything.

➔ Explore our catalogue of products on [TE.com](https://www.te.com)



Wire to Wire Connectors - Universal MATE-N-LOK




350767-1 03 POS UMNL CAP HSG V0

350778-1 02 POS UMNL CAP HSG

350780-1 04 POS UMNL CAP HSG

350866-1 01 POS UMNL CAP HSG



350766-1 03 POS UMNL PLUG HSG

350777-1 02 POS UMNL PLUG HSG

350779-1 04 POS UMNL PLUG HSG


350865-1 01 POS UMNL PLUG HSG



350551-2 UMNL SOK 20-14 AWG AUBR L/P

350689-2 UMNL SOK 24-18 AWG AUBR L/P

640310-6 UMNL SOK 12-10 AWG AU/PHBZ



350552-2 UMNL PIN 20-14 AWG AUBR L/P

350690-2 UMNL PIN 24-18 AWG AUBR L/P

640309-6 UMNL PIN 12-10 AWG AU/PHBZ


Wire to Wire - ULTRA FAST



2-520184-2 250 ULTRA-FAST RCPT 22-18 TPBR

3-350820-2 250 ULTRA-FAST RCPT 16-14 TPBR

4-520448-2 250 ULTRA FAST REC 12-10TPBR



2-520103-2 250 ULTRA-FAST TAB 22-18 TPBR

3-520107-2 250 ULTRA-FAST TAB 16-14 TPBR

4-521098-2 250 ULTRA-FAST TAB 12-10 TPBR

Heat Shrink Tubing - VERSAFIT (shrink ratio 2-1)




NB20364001 VERSAFIT-3/16-4-SP yellow

NB20394001 VERSAFIT-3/16-9-SP white


NB20344001 VERSAFIT-3/16-2-SP red

NB20084001 VERSAFIT-1/4-4-SP yellow


Wire to Wire/Panel Power Connectors



- 53884-1** HSG ASSY,PWR LK,SRS2,1 POS,BLU
53884-4 HSG ASSY,PWR LK,SRS2,1 POS,RED



- 53886-1** PNL MT ADAPTER,FEMALE,POWER LK



- 54330-1** CONTACT,PWR LK,SRS2,LS PC,SLDR, 6 awg max
53880-4 CONTACT,PWR LK,SRS2,LS PC,CRMP, 10-6 awg

Toggle Switches



- 1-1437558-2** MTA106E=(MSTA) SWITCH TOGGLE S, SPDT on-off-on
2-1437558-0 MTA206N=(MSTA) SW TOG DPDT, DPDT on-on

Microswitch



- 1825043-3** UPO1DTANLA04,MICROSWITCH,SNAP SPDT

Ring, Spade and Splice Terminals



- 34067** PG BUTT SPLC 22-16COMM22-18MIL
34071 SPLICE,PG BUTT 16-14
34072 SPLICE,PG BUTT 12-10



- 34150** PG R 22-16 COMM 22-18 MIL 1/4
34162 TERMINAL,PG R 16-14 1/4
34855 TERMINAL,PG R 12-10 1/4
52041-1 TERMINAL,R PG 8 1/4
52042-3 TERMINAL,R PG 6 1/4



- 34156** PG SPD 22-16 COMM 22-18 MIL 10
34176 TERMINAL,PG SPD 12-10 10

Terminal Block



- 1-1546670-4** 14P.437"" DR BARRIER,W/BND SCRW
1546670-3 3P .437"" DR BARRIER,W/BND SCRW
1546670-4 4P .437"" DR BARRIER,W/BND SCRW



- 2350397-3** 3 POS SPRING TB PLUG, PITCH 5.00
Tip: Fits great with "Robot Signal Light" (Allen Bradley 855PB-B12ME522). Spring style connector offers superior performance to standard screw connector.



- 1986723-2** STR PLUG SPRING TYPE RH 2P, 3.50mm
Tip: Fits great with NI RoboRIO microcontroller. Spring style connector offers superior performance to standard screw connector.

Popular Items!