

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2018

© COPYRIGHT 2018

BY - TE CONNECTIVITY

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER PCN E-18-015129	13DEC2018	SS	DM
	A2	DRAWING UPDATED	12MAR2024	RK	CB

5 MATERIAL: RECEPTACLE: PEI (BLACK); WELD RING: PEI (BLACK); WELD CAP: PEI (BLACK); INTERFACE SEAL: VMQ (RED-ORANGE)

4 DATE CODE: MONTH IS REPRESENTED BY SEQUENTIAL ALPHA CHARACTERS. EX: A = JANUARY. YEAR IS REPRESENTED BY LAST NUMERIC DIGIT. EX: 7 = 2007.

3. THIS RECEPTACLE MATES WITH DTHD06-1-4S-XXXX PLUG (XXXX= ALL MODIFICATIONS).

2. FOR "PERFORMANCE AND APPLICATION CHARACTERISTICS OF SOLID/STAMPED AND FORMED CONTACTS AND WIRES", SEE CUSTOMER DRAWING 0425-015-0000.

1. CONSULT FACTORY FOR ELECTRICAL AND MATERIAL SPECIFICATIONS.

NOTES:

TE INTERNAL PN	DEUTSCH PN	
DTHD04-1-4P-E003	DTHD04-1-4P-E003	
CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.
4	.261 [6.63]	.420 [10.67]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J. HAYNES	15SEP1999		RECEPTACLE POWER DT SIZE 4 HD CONTACTS -E003 MOD COLOR: BLACK
DIMENSIONS: INCHES [mm]		CHK	D. MEYER	15SEP1999		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	D. MEYER	16SEP1999		
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±.025 [0.64] 4 PLC ±- ANGLES ±0°30'0"		PRODUCT SPEC	108-151020			
MATERIAL	5	FINISH	-		APPLICATION SPEC	114-151020
		WEIGHT	14 g		SIZE	A3
		CUSTOMER DRAWING			CAGE CODE	4AFU8
		SCALE	2:1		DRAWING NO	DTHD04-1-4P-E003
		SHEET	1 OF 1		RESTRICTED TO	
		REV	A2			

1470-19 (3/13)