

AKII / AKII+ Squib Connectors for Airbag and Safety Applications (2 and 3 way 180°)

TE Connectivity (TE) is one of the world's leading companies in developing, manufacturing and supplying a full range of high quality, technologically advanced squib connectors & cable assemblies. Our products provide the reliability needed for critical safety applications such as airbags.

TE is a global technology company that can support customers in any region of the world and offers:

- Research and development capabilities, prototyping and samples
- TS 16949 and ISO 14001 certified manufacturing facilities
- Fully certified testing/validation laboratory
- High quality level ensured by automated production and EOL processes

Key Features

- Interface: AKII / AKII+ ISO 19072
- EMI Suppression: Ferrite
- Locking: CPA

AKII / AKII+ Squib Connectors for Airbag and Safety Applications

AKII 2 way 180° Squib

- 2 way 180° squib
- Wire Cross Section: 0.35 0.50 mm²
- Supplied as pigtails

Technical Specifications

Product Specification 108-15019 **Application Specification** 408-15438

Dimensions Height Length

12.9 mm 26.75 mm 16.0 mm

Part Numbers

Width

Specific to coding, length, type of wires and OEM. Contact TE Sales for details.


AKII 3 way 180° Squib


- 3 way 180° squib
- Wire Cross Section: 0.35 0.50 mm²
- Supplied as pigtails

Technical Specifications	Dimensions	
Product Specification	Height	12.9 mm
108-15019	Length	26.75 mm
Application Specification 408-15438	Width	16.0 mm

Part Numbers

Specific to coding, length, type of wires and OEM. Contact TE Sales for details.





AKII SCR Retainer, 11 mm Diameter

- Retainer with integrated shorting clip
- Supplied with and without clip
- To be mounted in the 11 mm ignitor
- To be used with 2 way connectors
- Selective gold plated contact points
- Retention improved with lugs
- Mechanical codings available

Technical Specification Product Specification


108-3645

Dimensions Height

Diameter

Part Number

1823640



www.te.com www.te.com/automotive For further information please go to: www.TE.com/support-center



TE Connectivity Germany GmbH Ampèrestrasse 12-14 64625 Bensheim | Germany

© 2018 TE Connectivity | All rights reserved. TE, TE Connectivity, and TE connectivity (logo) are trademarks.

1-1773945-1 | Published 06-2018 | PoD • RRD

Te Connectivity's (TE's) only obligations are those stated in TE's General Terms and Conditions of Business (www.te.com/usa-en/policies-agreements/terms-of-use-te-com/terms-conditions-sale.html). TE expressly disclaims any implied warranty regarding the information contained herein, including, but not limited to, the implied warranties of merchantability or fitness for a particular purpose



7.9 mm

11.0 mm