





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2008
 COPYRIGHT 2008 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DRN	APPD		
1		PROPOSED	01MAY2008	WJS	CR		
2		REVISED	08JUL2008	JKS	CR		



- △ MATERIAL:
CONTACT AND SHIELD: PHOS BRONZE
HOUSING AND CHICKLET: LCP, UL 94V-0, COLOR: BLACK
- △ FINISH: CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION, 108-2303-1; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III; APPLICATIONS IN CONTROLLED ENVIRONMENTS. (CENTRAL OFFICE)
- △ CONNECTOR MARKED WITH PART NUMBER, DATE CODE, 85 OHM, AND STANDARD IN APPROXIMATE AREA SHOWN.
- △ DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- △ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- △ FINISHED HOLE = $\phi 0.46 \pm 0.05$
 TYPICAL HOLE DETAIL:
 DRILLED HOLE = $\phi 0.55 \pm 0.05$
 COPPER THICKNESS = 0.038 ± 0.013
 TIN THICKNESS = 0.008 ± 0.004
 FINISHED HOLE = $\phi 0.46 \pm 0.05$
- △ THE GROUNDS IN EACH COLUMN ARE COMMONED.



PRELIMINARY - NOT
 RELEASED FOR PRODUCTION

THIS PRODUCT HAS NOT
 COMPLETED VALIDATION TESTING

1934951-1
 PART NUMBER

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN SOURBEER 01MAY2008		Tyco Electronics Harrisburg, PA 17105-3608	
0 PLC ± .1		1 PLC ± .1		CHK C. RITTER 01MAY2008		NAME RECEPTACLE ASSEMBLY, 3 PAIR, 10 COLUMN Z-PACK TinMan 85 OHM	
2 PLC ± .1		3 PLC ± .1		APVD		PRODUCT SPEC	
4 PLC ± .1		ANGLES ± .1		APPLICATION SPEC		SIZE	
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
CUSTOMER DRAWING		SCALE 6:1		SHEET 1 OF 1		REV 2	