




NOTES:

1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.

2. PARTS SHALL BE BAGGED 25PCS PER BAG WITH HP PART NUMBER AND BARCODE ON BAG EXTERIOR.

3. LABEL REQUIREMENTS:

3.1 LABEL SHALL BE MARKED WITH DATECODE,NAME OF MANUFACTURE,AND "PRODUCT OF CHINA" IN HUMAN-READABLE FONT,AND WITH HP PART NUMBER IN BOTH HUMAN-READABLE AND BARCODE FONTS.

3.2 DATECODE FORMAT:WEEK/YEAR(WW/YY).

3.3 HUMAN-READABLE FONT HEIGHT:3mm MIN. BARCODE FONT HEIGHT:8mm MIN.

3.4 BARCODE SHALL BE CODE 39(GENERAL)WITHOUT CHECKSUM. BARCODE SHALL CONSIST OF HP PART NUMBER PLUS START/STOP CHARACTERS. ADHERENCE TO ANSI MH10.8M IS REQUIRED. QUIET ZONE 5mm MIN ON BOTH ENDS BARCODE.

-	-	1	PC	LABEL:110*30MM, WHITE: 25*30MM	10
1	1	1	PC	HOUSING, IDC TYPE, FOR 22AWG WIRE, TYU: TU6012HNO-05YE-2A-V2	9
1	1	1	PC	SATA PLUG, 7PIN CONTACT: GOLD 15U" PLATED, BLACK, MATERIAL: LCP	8
AR	AR	AR	MR	HOOK UP WIRE, UL 1007, 22AWG, COLOR: RED	7
AR	AR	AR	MR	HOOK UP WIRE, UL 1007, 22AWG, COLOR: YELLOW	6
AR	AR	AR	MR	HOOK UP WIRE, UL 1007, 22AWG, COLOR: BLACK	5
AR	AR	AR	MR	SATA CABLE, UL20276, SOLID TYPE, (26AWG*2CDRAIN*2+AL/MYLAR)*2, COLOR: RED(RD09)	4
AR	AR	AR	KG	OVER MOLDED PVC 40P,BLACK(BK01)	3
AR	AR	AR	KG	INNER MOLDED PE, COLOR: CLEAR	2
1	1	1	PC	SATA, RECEPT, 7P+15P, CONTACT: GOLD FLASH, SOLDER, BLACK	1
-3	-2	-1	U/M		

DIMENSIONS:				TOLERANCES UNLESS OTHERWISE SPECIFIED:		DESCRIPTION		ITEM	
mm									
				0 PLC	± -	DWN 22NOV06 CHK ARTHUR ZHANG LAWRENCE LV APVD POND TAN PRODUCT SPEC APPLICATION SPEC WEIGHT - CUSTOMER DRAWING		TE Connectivity SATA, 7P+15P TO 7P(STRAIGHT)+5P(IDC) - SIZE A2 CAGE CODE 00779 DRAWING NO C=1453749 RESTRICTED TO -	
				1 PLC	± -				
				2 PLC	± -				
				3 PLC	± -				
				4 PLC	± -				
MATERIAL -				FINISH -		SCALE N.T.S.		SHEET 1 of 1	

1471-9 (3/11)