







- | | | | |
|----------|-------------|--------------|---|
| | TE PART NO. | NANONICS P/N | FINISH |
| | 1589953-1 | QCM007M5P |  |
| OBSOLETE | 1589953-2 | QCB007M5P |  |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MORALES CHK 23APR2007		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± .01 3 PLC ± .005 4 PLC ± — ANGLES ± 5°		NAME RECEPTACLE ASSEMBLY, CIRCULAR, VERTICAL MOUNT THRU-HOLE, .050 INCH LEAD PITCH, 7 POSITION, ELECTROLESS NICKEL SHELL AND JAM NUT FINISH	
MATERIAL SEE NOTES		FINISH — WEIGHT —		SIZE A2	CAGE CODE OPJN9
CUSTOMER DRAWING				DRAWING NO C-1589953	RESTRICTED TO —
				SCALE 6:1	SHEET 1 of 1
				REV D	