

CHEMINAX100 OHM, AWG 26, 19 STRANDS OF AWG 38, UNSHIELDED,
UNJACKETED, TWO CONDUCTOR CABLE


Date: 10-10-06

Revision: B

THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.

CONSTRUCTION DETAILS

DIMENSIONS ARE NOMINAL VALUES IN INCHES UNLESS OTHERWISE DESIGNATED.

**ELECTRICAL CHARACTERISTICS**

CHARACTERISTIC IMPEDANCE 100 ± 10 ohms, Method C at 1 MHz

CAPACITANCE 16.0 pF/ft. (nominal)

ADDITIONAL REQUIREMENTS**COMPONENT WIRE PRIOR TO CABLING (Test Procedures per AS22759)**

CROSSLINK PROOF 300 ± 3°C for 1 hour,
.375 inch mandrel, .187 lb.,
2.5 kV dielectric test

LOW TEMPERATURE
COLD BEND -65 ± 2°C for 4 hours,
.500 inch mandrel, 0.500 lb.,
2.5 kV dielectric test

SHRINKAGE 200 ± 3°C for 1 hour, .125 inch
(maximum) in 12 inches

INSULATION RESISTANCE 5000 megohms for 1000 ft. (minimum)

INSULATION (DIELECTRIC)
TENSILE STRENGTH 5000 lbf/in² (minimum)

ELONGATION 50% (minimum)

INSULATION FLAWS
SPARK TEST 3.0 kV (rms)

IMPULSE TEST 8.0 kV (peak)

INSULATION WALL THICKNESS .005 ± .001 inch

FINISHED CABLE

INSULATION FLAWS
SPARK TEST 3.0 kV (rms)

IMPULSE TEST 8.0 kV (peak)

WEIGHT 2.4 lbs/1000 ft. (nominal)

Other codes and suffixes may be added to the part number, as necessary, to capture any additional requirements imposed by the purchase order.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

tyco
Electronics

Raychem
Wire & Cable

501 Oakside Avenue
Redwood City, California 94063-3800
1-800-227-8816 Fax: 1-650-361-6297

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

© 2006 Tyco Electronics Corporation. All rights reserved.