


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REV PER ECN-24-273566	03JUL2024	JAB	JG
	D	REVISED PER ECN-24-278675	22AUG2024	PE	JG
	E	REV PER ECN-25-303030	21JAN2025	JAB	MN

COMPONENT	MATERIAL	FINISH
FRONT SHELL	BeCu PER ASTM B196	SILVER PLATE PER ASTM B700
SHELL	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
COLLAR	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
GASKETS	SILICONE RUBBER PER A-A-59588	N/A
SPRING	BeCu PER ASTM B194	TIN PLATE PER ASTM B545
WASHER	BRASS PER ASTM B36	SILVER PLATE PER ASTM B700
MALE CONTACT	BRASS PER ASTM B16	GOLD PLATE PER ASTM B488 OVER NICKEL PLATE PER SAE-AMS-QQ-N-290
SPACER	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
SHELL	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
CRIMP FERRULE	COPPER OR BRASS ALLOY ROCKWELL B 45 MAX	SILVER PLATE PER ASTM B700



WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

RECOMMENDED CABLE PREPARATION

69814	69710-1	131223-1
DIE SET	CRIMP TOOL	PART NUMBER

1. FOR USE WITH KX23 (RG400U) COAX CABLE.

2 PART NO "131223-1" MARKED ON INDICATED SURFACE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.A.BAKER 03JUL2024	TE Connectivity TE BNC, PLUG ASSEMBLY		
DIMENSIONS: mm		CHK J.GUNDERMANN 03JUL2024			
		APVD D.WILSON 03JUL2024			
		PRODUCT SPEC 108-12002			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 408-1799	NAME		
0 PLC ±-		WEIGHT 16 G	SIZE A3	CAGE CODE -	DRAWING NO C-131223
1 PLC ±.1		RESTRICTED TO			
2 PLC ±.05		SCALE 2:1			
3 PLC ±-		SHEET 1 OF 1			
4 PLC ±-		REV E			
ANGLES ±-					
FINISH					
-					
-					