




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECO-09-023020	14OCT2009	HMR	CR
	A2	NEW PN 3-1986525-2 ADDED	16OCT2024	NMP	PS

1. MATERIALS AND FINISH:
HOUSING: PA 6-6, UL94V-0, COLOR: REFER TABLE
TERMINALS: PHOSPHOR BRONZE, TIN PLATED
6-7µm OVER 2-3µm NICKEL UNDERPLATE.
2. SUITABLE FOR 1.6-2.4mm PC BOARD THICKNESS.
3. NOT CUMULATIVE TOLERANCE.
4. OPERATING TEMPERATURE RANGE: -40°C TO +110°C.
5. CURRENT RATING: 300V, 15A
6. UL RECOGNIZED TO CANADIAN AND US STANDARDS
IN FILE E60677.
7. 2 POSN HEADER WILL MATE WITH 284046-2
4 POSN HEADER WILL MATE WITH 284046-4.


8 3-1986525-2 PRELIMINARY



SECTION D - D



1986525-2 AS SHOWN



RECOMMENDED PC BOARD LAYOUT

RAL (2003)	12.0	2	3-1986525-2
RAL (6032)	22.0	4	1986525-4
RAL (6032)	12.0	2	1986525-2
RALREF	DIM A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 02MAR2009	TE Connectivity		
DIMENSIONS: mm		CHK C RICHARD 02MAR2009			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C RICHARD 02MAR2009			
0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±0.25 4 PLC ±0.25 ANGLES ±0.25		PRODUCT SPEC			
MATERIAL		FINISH	NAME TERMINAL BLOCK, HIGH RISE, 5.0mm PITCH		
			APPLICATION SPEC		
			WEIGHT		
			CUSTOMER DRAWING		
			SIZE A3	CAGE CODE 00779	RESTRICTED TO -
			DRAWING NO C-1986525	SCALE 3:1	REV A2
			SHEET 1	OF 1	