


- 1 CABLE ASSEMBLY TESTED FOR OPENS, SHORTS AND HI-POT @ 300V.
- 2 LABEL INFORMATION:

	2127833-	← TE LOGO & TE CONNECTIVITY PART NUMBER
MINI-SAS	6Gbps	
---	METERS	← LENGTH
YYWW		← DATE CODE
MADE IN	---	← COUNTRY OF ORIGIN
- 3. PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY STANDARD TEC-138-702.
- 4. PRODUCT MEETS THE REQUIREMENTS OF T10/2125-D, REVISION 04b [SAS-2.1].

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SMITH 24FEB2010	TE Connectivity																		
DIMENSIONS: mm		CHK J.HACKMAN 24FEB2010																			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.HACKMAN 24FEB2010	NAME CABLE ASSEMBLY, MINI-SAS, 4X, EXTERNAL 6 Gbps, PASSIVE																		
<table border="1"> <tr> <td>0 PLC</td> <td>±</td> <td>-</td> </tr> <tr> <td>1 PLC</td> <td>±</td> <td>-</td> </tr> <tr> <td>2 PLC</td> <td>±</td> <td>-</td> </tr> <tr> <td>3 PLC</td> <td>±</td> <td>-</td> </tr> <tr> <td>4 PLC</td> <td>±</td> <td>-</td> </tr> <tr> <td>ANGLES</td> <td>±</td> <td>°</td> </tr> </table>		0 PLC	±	-	1 PLC	±	-	2 PLC	±	-	3 PLC	±	-	4 PLC	±	-	ANGLES	±	°	APPLICATION SPEC	SIZE A1
0 PLC	±	-																			
1 PLC	±	-																			
2 PLC	±	-																			
3 PLC	±	-																			
4 PLC	±	-																			
ANGLES	±	°																			
MATERIAL	FINISH	WEIGHT	CAGE CODE 00779																		
DRAWING NO 2127833		RESTRICTED TO																			
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 2																		



3	3	2-4-6	2-4-6	6 GBPS	24 AWG	10±0.15 METERS	2-2127833-6
3	3	2-4-6	2-4-6	6 GBPS	24 AWG	9±0.15 METERS	2-2127833-5
3	3	2-4-6	2-4-6	6 GBPS	24 AWG	8±0.125 METERS	2-2127833-4
3	3	2-4-6	2-4-6	6 GBPS	24 AWG	7±0.1 METERS	2-2127833-3
-	-	2-4-6	2-4-6	6 GBPS	24 AWG	6±0.075 METERS	2-2127833-2
-	-	2-4-6	2-4-6	6 GBPS	24 AWG	5±0.075 METERS	2-2127833-1
-	-	2-4-6	2-4-6	6 GBPS	26 AWG	4±0.075 METERS	2-2127833-0
-	-	2-4-6	2-4-6	6 GBPS	26 AWG	3±0.05 METERS	1-2127833-9
-	-	2-4-6	2-4-6	6 GBPS	28 AWG	2.5±0.05 METERS	1-2127833-8
-	-	2-4-6	2-4-6	6 GBPS	28 AWG	2±0.05 METERS	1-2127833-7
-	-	2-4-6	2-4-6	6 GBPS	28 AWG	1.5±0.04 METERS	1-2127833-6
-	-	2-4-6	2-4-6	6 GBPS	30 AWG	1±0.04 METERS	1-2127833-5
-	-	2-4-6	2-4-6	6 GBPS	30 AWG	0.5±0.025 METERS	1-2127833-4
3	3	2-4	4-6	6 GBPS	24 AWG	10±0.15 METERS	1-2127833-3
3	3	2-4	4-6	6 GBPS	24 AWG	9±0.15 METERS	1-2127833-2
3	3	2-4	4-6	6 GBPS	24 AWG	8±0.125 METERS	1-2127833-1
3	3	2-4	4-6	6 GBPS	24 AWG	7±0.1 METERS	1-2127833-0
-	-	2-4	4-6	6 GBPS	24 AWG	6±0.075 METERS	2127833-9
-	-	2-4	4-6	6 GBPS	24 AWG	5±0.075 METERS	2127833-8
-	-	2-4	4-6	6 GBPS	26 AWG	4±0.075 METERS	2127833-7
-	-	2-4	4-6	6 GBPS	26 AWG	3±0.05 METERS	2127833-6
-	-	2-4	4-6	6 GBPS	28 AWG	2.5±0.05 METERS	2127833-5
-	-	2-4	4-6	6 GBPS	28 AWG	2±0.05 METERS	2127833-4
-	-	2-4	4-6	6 GBPS	28 AWG	1.5±0.04 METERS	2127833-3
-	-	2-4	4-6	6 GBPS	30 AWG	1±0.04 METERS	2127833-2
-	-	2-4	4-6	6 GBPS	30 AWG	0.5±0.025 METERS	2127833-1
P1	P2	P1	P2	DATA RATE	WIRE GAGE	L	PART NO
KEY RIB		KEY SLOTS					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DRAWING NO	RESTRICTED TO
0. PLC ± -	1. PLC ± -	24FEB2010	
2. PLC ± -	3. PLC ± -	24FEB2010	
4. PLC ± -	ANGLES ± -		
MATERIAL	FINISH	WEIGHT	SCALE
			1:1

APPROVED: J. HACKMAN, 24FEB2010

TE Connectivity

CABLE ASSEMBLY, MINI-SAS, 4X, EXTERNAL
6 Gbps, PASSIVE

SIZE: A1, CAGE CODE: 00779, DRAWING NO: 2127833

CUSTOMER DRAWING, SCALE: 1:1, SHEET 2 OF 2, REV B1