Thermofit Molded Parts Specification Control Drawing Limited Distribution

Part Number : 222D921-X-02 Description : Boot, 90°



1. All dimensions are in $\frac{\text{incnes}}{[\text{millimeters}]}$

- 2. Dimensions appearing in table are as follows:
 - a As Supplied
 - b After Unrestricted Recovery
- Coating is optional. As supplied dimensions appearing in table are for uncoated ports. When coating is added, entry diameters will be reduced by .06 max.
- 4. Molding port is required. And will be located as shown.




TABLE OF DIMENSIONS										
PART	Н		J		Р	R	U	JO	нw	JW
NÜMBER	Min	Max	Min	Max	±10%	Ref	±10%	±10%	±20%	±20%
	a	ь	a	b	b	b	b	ь	ь	b
222D921-X-02	.76 [19,3]	.51 [13,0]	.25 [6,3]	.08 [2,1]	1.75 [44,5]	.45 [11,4]	.22 [5,6]	.86 [21,8]	.06 [1,52]	. <u>045</u> [1,14]
	[10,0]	[10,0]	[0,0]	[2,1]	[,0]	F11,-43	[0,0]	[21,0]	[1,02]	F141-43



RAYCHEM CORPORATION 300 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025

Revision: A Date: 10/16/96

222D921-X-02 Part Number :


Description: Boot, 90°

Thermofit Molded Parts Specification Control Drawing

Limited Distribution

Part Number :	222D921-X-02			
Description :	Boot, 90°			

COMPATABILITY	CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-3	Polyolefin, Semi-rigid	RT-301	/42; /86	S-1017; S-1048	Adhesive
-4	Polyolefin, Flexible	RT-1304	/42; /86	S-1017; S-1048	Adhesive
-25	Elastomer, Fluid Resistant	RT-1325	/86	S-1048	Adhesive



THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE: CONSULT YOUR NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

If this document is printed it becomes uncontrolled. Check for the latest revision.

Raychem

RAYCHEM CORPORATION 300 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025

Revision: A Date: 10/16/96 Part Number : 222D921-X-02

Description: Boot, 90°

CAD FILE MP96578