


© - TE Connectivity. All Rights Reserved.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	G5	REVISED PER ECR-25-255998	15SEP2025	SA DSC



AMP WIRE RANGE	E13288 Listed	LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED

- 1 BODY MATERIAL THICKNESS = 0.787±0.051 [.031±.002]
- 2 FOR Ø2.667[Ø.105] TO Ø3.556[Ø.140] WIRE INSULATION.
- 3 STAMP AMP 22-18* APPROX AS SHOWN.
22-16 TERMINALS ARE STAMPED
22-18 IN ACCORDANCE WITH
MILITARY SPEC SAE AS 7928.
COMMERCIAL RANGE IS 22-16.
- 4 APPLIES FROM EDGE OF METAL WIRE BARREL TO
CENTER OF STUD HOLE.
- 5 MATERIAL:
BODY & SLEEVE: COPPER (ASTM-B152)
INSULATION: NYLON.
- 6 FINISH:
BODY & SLEEVE: TIN PLATED (ASTM-B545)
INSULATION: COLOR-RED.

1 KIT = 250 PIECES	LOOSE PIECE	6-326861-0
5000	ON TAPE	2-326861-1
1000	LOOSE PIECE	326861
QTY	PACKAGE TYPE	PART NO

CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 15JUL09	TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK TOM MICHIELUTTI 15JUL09				
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-1.65mm² [509-3,260] SOLID OR STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± .5°	APVD TOM MICHIELUTTI 15JUL09	PRODUCT SPEC UL 486 A-B			
FOR ORDER ENTRY	1-800-526-5142		MATERIAL	FINISH	APPLICATION SPEC 114-2157	SIZE A3	CAGE CODE 00779	DRAWING NO G-326861	RESTRICTED TO
					WEIGHT -	SCALE 5:1		SHEET 1 OF 1	REV G5