## SPECIFICATION CONTROL DRAWING

44A9615

TITLE


TWO CONDUCTOR CABLE, UNSHIELDED, UNJACKETED, GENERAL PURPOSE, 600 VOLT Date

8-20-93

Revision

В

This specification sheet forms a part of the latest issue of Raychem Specification 44.



CABLE CONSTRUCTION DETAILS				
PART NUMBER	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inches)		NOMINAL WEIGHT (lbs/1000 ft.)
		NOMINAL	MAXIMUM	
44A9615-26-*	26	.068	.072	2.9

## CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C
Maximum continuous conductor temperature
VOLTAGE RATING: 600 volts (rms)
\* BLOCKING: 150 ± 3°C for 6 hours
Adjacent layers shall not stick togther
CABLE LAY: 0.50 ± .06 right hand lay
DIELECTRIC WITHSTAND: 2500 volts (rms),
60 Hz, for 1 minute.

FLAMMABILITY: 30 seconds (maximum); 3 in. (maximum); no flaming of facial tissue

\* Qualification test

## PART NUMBER:

The "\*" in the part number above shall be replaced by a color code designator with a slash separating component wire colors: Example: White and black component wires: 44A9615-26-9/0

NOTE: Nominal values are for information only.

Nominal values are not requirements.

COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL

RENCED 300 C

Raychem Corporation 300 Constitution Drive, Menlo Park, California 94025 1-800-2 Raychem FAX: 1-415-361-6297

Raychem