



SPECIFICATION CONTROL DRAWING		SCD		44A083X																																																																									
Title THREE CONDUCTOR CABLE, UNSHIELDED, UNJACKETED, 600 VOLT		Date 11-11-15		Revision H																																																																									
This specification sheet forms a part of the latest issue of Raychem Specification 44.																																																																													
<div style="margin-bottom: 20px;"> <p>COMPONENT WIRES - 44A081X</p>  </div> <div style="text-align: center;"> <table border="1" style="width: 100%; border-collapse: collapse; font-size: 0.8em;"> <tr> <th colspan="5">CABLE CONSTRUCTION DETAILS</th> </tr> <tr> <th rowspan="2">PART NUMBER 1/</th> <th rowspan="2">CONDUCTOR SIZE (AWG)</th> <th colspan="2">OUTSIDE DIAMETER (inch)</th> <th rowspan="2">MAXIMUM WEIGHT (lbs/1000 ft.)</th> </tr> <tr> <th>NOMINAL</th> <th>MAXIMUM</th> </tr> <tr><td>44A083X-26-*</td><td>26</td><td>.104</td><td>.108</td><td>5.8</td></tr> <tr><td>44A083X-24-*</td><td>24</td><td>.117</td><td>.121</td><td>8.3</td></tr> <tr><td>44A083X-22-*</td><td>22</td><td>.134</td><td>.140</td><td>11.9</td></tr> <tr><td>44A083X-20-*</td><td>20</td><td>.151</td><td>.158</td><td>16.8</td></tr> <tr><td>44A083X-18-*</td><td>18</td><td>.173</td><td>.179</td><td>24.5</td></tr> <tr><td>44A083X-16-*</td><td>16</td><td>.192</td><td>.201</td><td>30.9</td></tr> <tr><td>44A083X-14-*</td><td>14</td><td>.233</td><td>.242</td><td>47.4</td></tr> <tr><td>44A083X-12-*</td><td>12</td><td>.272</td><td>.281</td><td>70.4</td></tr> <tr><td>44A083X-10-*</td><td>10</td><td>.335</td><td>.346</td><td>109.</td></tr> <tr><td>44A083X-8-*</td><td>8</td><td>.462</td><td>.475</td><td>192.</td></tr> <tr><td>44A083X-6-*</td><td>6</td><td>.570</td><td>.585</td><td>304.</td></tr> <tr><td>44A083X-4-*</td><td>4</td><td>.691</td><td>.708</td><td>468.</td></tr> </table> </div> <div style="text-align: center; margin-top: 20px;"> <p>CABLE RATINGS AND ADDITIONAL REQUIREMENTS</p> <div style="display: flex; justify-content: space-between;"> <div style="width: 45%;"> <p>TEMPERATURE RATING: 150°C Maximum continuous conductor temperature</p> <p>VOLTAGE RATING: 600 volts (rms) at sea level</p> <p>DIELECTRIC WITHSTAND: 2500 volts (rms), 60 Hz, 1 minute</p> <p>INSULATION FLAWS: Spark Test, 5.7 kV (rms) at 3 kHz Impulse Dielectric Test, 8.0 kV (peak)</p> </div> <div style="width: 45%;"> <p>1/ PART NUMBER: The "X" in the part numbers above shall be replaced with a conductor material designator as follows:</p> <ol style="list-style-type: none"> 1 tin-coated copper 2 silver-coated copper (AWG 24-4 only) 3 nickel-coated copper (AWG 24-12 only) 4 silver-coated high-strength copper alloy (AWG 26-20 only) <p>The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors. Colors shown do not necessarily reflect the sequence of manufacturing.</p> <p>Example: AWG 20, tin-coated copper conductors; black, brown, and red component wires: 44A0831-20-0/1/2</p> </div> </div> </div> <p style="margin-top: 20px;">NOTE: Nominal values are for information only. Nominal values are not requirements.</p>						CABLE CONSTRUCTION DETAILS					PART NUMBER 1/	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)	NOMINAL	MAXIMUM	44A083X-26-*	26	.104	.108	5.8	44A083X-24-*	24	.117	.121	8.3	44A083X-22-*	22	.134	.140	11.9	44A083X-20-*	20	.151	.158	16.8	44A083X-18-*	18	.173	.179	24.5	44A083X-16-*	16	.192	.201	30.9	44A083X-14-*	14	.233	.242	47.4	44A083X-12-*	12	.272	.281	70.4	44A083X-10-*	10	.335	.346	109.	44A083X-8-*	8	.462	.475	192.	44A083X-6-*	6	.570	.585	304.	44A083X-4-*	4	.691	.708	468.
CABLE CONSTRUCTION DETAILS																																																																													
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)																																																																									
		NOMINAL	MAXIMUM																																																																										
44A083X-26-*	26	.104	.108	5.8																																																																									
44A083X-24-*	24	.117	.121	8.3																																																																									
44A083X-22-*	22	.134	.140	11.9																																																																									
44A083X-20-*	20	.151	.158	16.8																																																																									
44A083X-18-*	18	.173	.179	24.5																																																																									
44A083X-16-*	16	.192	.201	30.9																																																																									
44A083X-14-*	14	.233	.242	47.4																																																																									
44A083X-12-*	12	.272	.281	70.4																																																																									
44A083X-10-*	10	.335	.346	109.																																																																									
44A083X-8-*	8	.462	.475	192.																																																																									
44A083X-6-*	6	.570	.585	304.																																																																									
44A083X-4-*	4	.691	.708	468.																																																																									
Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.																																																																													
1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.																																																																													
Page 1 of 1	Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.		 <div style="font-size: 0.7em; margin-top: 5px;"> Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297 </div>																																																																										
	DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL																																																																												
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.																																																																												