

SPECIFICATION CONTROL DRAWING

55PC1123

TITLE

TWO CONDUCTOR CABLE, SHIELDED, JACKETED, 600 VOLT

Date

08-07-01

Revision


A

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

COMPONENT WIRES - 55PC0113

SHIELD - NICKLE-COATED COPPER

JACKET - RADIATION-CROSSLINKED,
MODIFIED ETFE



CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
			LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC1123-26-*	26	38	.0050	.0065	.088	.092	.096	6.86	7.22
55PC1123-24-*	24	38	.0050	.0065	.097	.101	.105	8.55	8.91
55PC1123-22-*	22	38	.0050	.0065	.109	.114	.119	11.10	11.60
55PC1123-20-*	20	38	.0055	.0070	.126	.130	.134	14.95	15.44
55PC1123-18-*	18	38	.0055	.0070	.145	.149	.154	20.40	21.03
55PC1123-16-*	16	38	.0055	.0070	.159	.164	.169	24.81	25.54
55PC1123-14-*	14	38	.0060	.0075	.189	.194	.199	35.52	36.41
55PC1123-12-*	12	38	.0060	.0080	.227	.233	.238	51.71	52.88
55PC1123-10-*	10	36	.0065	.0085	.280	.291	.302	81.65	85.95

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

CROSSLINKING PROOF TEST: 300 ± 3°C for 1 hour

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms), 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100 % test

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by a color code designator with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 22, white and black component wires;
white jacket: 55PC1123-22-9/0-9

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

Raychem

300 Constitution Drive, Menlo Park, California 94025
1-800-2 RAYCHEM FAX: 1-650-361-6297