
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.


LOC	DIST
CM	53

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REACT & REDWN PER EC 0730-0171-96	6-25-96	BL	RS

1. WIRE RANGE: 20-14 (0.5-2mm²) AWG
   INSULATION RANGE: .125 MAX.





SECTION A–A
SCALE 10:1



SECTION B–B
SCALE 10:1

.050	1.27	.139	3.53	.180	4.57		
.043	1.09	.135	3.43	.165	4.19		
.035	0.89	.130	3.30	.157	3.99		
.018	0.46	.125	3.18	.156	3.96	.935	23.75
.015	0.38	.115	2.92	.155	3.94	.915	23.24
.005	0.13	.063	1.60	.154	3.91	.189	4.80
IN	MM	IN	MM	IN	MM	IN	MM

CONVERSION TABLE

TIN	.018 BRASS	61251-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±.005
4 PLC ±-
ANGLES ±-

MATERIAL BRASS
FINISH PRE-TIN

METRIC

DWN B. LEWIS 6-25-96
CHK R. SWING 6-25-96
APVD C. MARTIN 6-25-96
PRODUCT SPEC –
APPLICATION SPEC –
WEIGHT –
CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608

NAME PIN, LOOSE PIECE, .156 MATE-N-LOK™

SIZE	CAGE CODE	DRAWING NO
A2	00779	C-61251

SCALE	SHEET	REV
5:1	1 OF 1	B

61251

AMP 1471-9 REV 23FEB95

29-MAY-96 22:44:47 amp20569 /home/amp20569/medusa/u.new156/u.dwgs