

SPECIFICATION CONTROL DRAWING

55PC6193

TITLE

THREE CONDUCTOR CABLE, DOUBLE SHIELDED, JACKETED, 600 VOLT

Date


04-05-01

Revision

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

COMPONENT WIRES - 55PC0216

SHIELDS - NICKEL-COATED COPPER

JACKET - RADIATION-CROSSLINKED,
MODIFIED ETFE

CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	INNER SHIELD SIZE (AWG)	OUTER SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
				LOWERSPEC LIMIT	TARGET WALL	LOWERSPEC LIMIT	TARGET VALUE	UPPERSPEC LIMIT	TARGET VALUE	UPPERSPEC LIMIT
55PC6193-24-*	24	38	38	.0060	.0075	.131	.136	.141	18.19	18.86
55PC6193-22-*	22	38	38	.0060	.0075	.144	.149	.154	22.44	23.16
55PC6193-20-*	20	38	38	.0060	.0080	.164	.169	.174	29.16	29.98
55PC6193-18-*	18	38	38	.0060	.0080	.184	.189	.194	38.20	39.21
55PC6193-16-*	16	38	38	.0060	.0080	.200	.205	.210	45.43	46.52

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

CROSSLINKING PROOF TEST: 300 ± 3°C for 1 hour

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms), 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100 % test

SHIELD COVERAGE: 85% (minimum) (each)

VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 22, red, blue and yellow component wires; white

jacket: 55PC6193-22-2/6/4-9

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

Raychem300 Constitution Drive, Menlo Park, California 94025
1-800-2 Raychem Fax: 1-650-361-6297