


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	PART OBSOLESCENCE	03JUL2024	AR	VG

POS. PER PER	L±0.4	PART-NO.	
1	2.54	-----1	3
2	5.08	-----2	3
3	7.62	-----3	
4	10.16	-----4	3
5	12.70	-----5	
6	15.24	-----6	3
7	17.78	828296 -7	
8	20.32	-----8	
9	22.86	-----9	3
10	25.40	1-----0	3
11	27.94	1-----1	3
12	30.48	1-----2	
13	33.02	1-----3	
14	35.56	1-----4	
15	38.10	1-----5	3
16	40.64	1-----6	3
17	43.18	1-----7	3
18	45.72	1-----8	3
19	48.26	1-----9	3
20	50.80	2-----0	
21	53.34	2-----1	3
22	55.88	2-----2	3
23	58.42	2-----3	3
24	60.96	2-----4	3
25	63.50	2-----5	3
26	66.04	2-----6	3
27	68.58	2-----7	3
28	71.12	2-----8	3
29	73.66	2-----9	3
30	76.20	3-----0	3
31	78.74	3-----1	3
32	81.28	3-----2	3
33	83.82	3-----3	3
34	86.36	3-----4	3
35	88.90	3-----5	3
36	91.44	3-----6	3
37	93.98	3-----7	3
38	96.52	3-----8	3
39	99.06	3-----9	3
40	101.60	4-----0	
41	104.14	4-----1	3
42	106.68	4-----2	3
43	109.22	4-----3	3
44	111.76	4-----4	3
45	114.30	4-----5	3
46	116.84	4-----6	3
47	119.38	4-----7	3
48	121.92	4-----8	3
49	124.46	4-----9	OBSOLETE 2
50	127.00	5-----0	




- 1 MATING SIDE: Min 0.76µm (PdNi + Au FLASH)IN ZONE "F" OVER
Min 1.27µm Ni
(Alternative plating - Min 0.76µm Au OVER Min 1.27µm Ni)
SOLDER SIDE: MIN. 2.5µm TIN OVER Min 1.27µm NICKEL
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 3 OBSOLETE

1	CONTACT PIN	CuZn	2
COLOUR:GREEN	PIN HOUSING	PBT	1
FINISH/COLOR	PART DESCRIPTION	MATERIAL	ITEM NO.

TE Connectivity. All Rights Reserved.



DIMENSIONS:		DWN	17AUG1989	MATERIAL		FINISH							
mm		G.Holaus		SEE TABLE		SEE TABLE							
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		CHK	M.Schaarschmidt	TE Connectivity									
		APVD	—										
		PRODUCT SPEC		NAME									
		108—18012											
		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
—													
		WEIGHT		A4		00779		C—828296		—			
		CUSTOMER DRAWING		SCALE		4:1		SHEET		1 OF 1		REV	