

SPECIFICATION CONTROL DRAWING

62A6002

TITLE

CABLE, ELECTRIC, TIN-COATED COPPER STRAND WIRE,
MODIFIED POLYESTER INSULATED

Date

1-14-98


Revision

C

This specification sheet forms a part of the latest issue of Raychem Specification 62.

STRANDED WIRE - TIN-COATED COPPER

INSULATION - MODIFIED POLYESTER



CONSTRUCTION DETAILS						
PART NUMBER	STRANDED WIRE				FINISHED CABLE	
	SIZE (AWG)	STRANDING (number x AWG)	MAXIMUM DIAMETER (in.)	MAXIMUM RESISTANCE AT 20°C (ohms/1000 ft.)	DIAMETER (in.)	NOMINAL WEIGHT (lbs/1000 ft.)
62A6002-22-*	22	154 x 44	.033	18.8	.047 ± .002	2.8

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE INDEX: 3000 hours (minimum)
at 150°C

VOLTAGE RATING: 600 volts (rms)

CONCENTRICITY: 70% (minimum)

FLAMMABILITY: 70 seconds (maximum) afterburn

INSULATION ELONGATION AND TENSILE STRENGTH:

Elongation, 250% (minimum)

Tensile Strength, 4000 lbf/in² (minimum)

INSULATION CONTINUITY PROOF TEST:

Impulse Dielectric Test, 8.0 kV (peak)

INSULATION THICKNESS: .008 inch (nominal)

SHRINKAGE: .050 inch (maximum)

THERMAL STABILITY: 165°C for 168 hours,
80% (minimum) retention of Tensile Strength,
50% (minimum) retention of Elongation

PART NUMBER:

The "*" in the part number shall be replaced
by a color code designator per Spec. 62.

Example: White insulation: 62A6002-22-9

COLORS SHALL BE IN ACCORDANCE WITH SAE J1128

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

Page 1 of 1

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED
DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.**Raychem**Raychem Corporation
300 Constitution Drive, Menlo Park, California 94025
1-800-2 Raychem Fax: 1-650-381-6297