






LOC		DIST		REVISIONS			
AD	0	REV	DATE	BY	CHK	APPV	
AE1	REVISED PER ECO-11-004820		11MAR11	RK	HMR		

- RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
- TUBE LOADED FOR AUTOMATIC INSERTION.
- TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.



RECOMMENDED MOUNTING HOLE PATTERN
SCALE 4:1

REVISION	DATE	BY	CHK	APPV	DESCRIPTION
1	2-20-87	M. CYRUS			GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK
2	2-20-87	R. MILLER			GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK
3	2-22-87	J. LAMBERT			GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK
4					GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK

OBSOLETE		TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640463-5
SUPERSEDED BY 390261-2		4	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640463-4
SUPERSEDED BY 390261-2		TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640463-3
SUPERSEDED BY 390261-2		4	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640463-2
SUPERSEDED BY 390261-2		TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-640463-1

CONTACT FINISH		CONTACT MAT'L		HOUSING MATERIAL		PART NO.
----------------	--	---------------	--	------------------	--	----------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 2-20-87		M. CYRUS	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		R. MILLER	
0 PLC ± -		1 PLC ± -		J. LAMBERT	
1 PLC ± -		2 PLC ± -		2-22-87	
2 PLC ± -		3 PLC ± .005		NAME	
3 PLC ± -		4 PLC ± -		PRODUCT SPEC	
4 PLC ± -		ANGLES ± -		108-1066	
MATERIAL SEE TABLE		FINISH SEE TABLE		APPLICATION SPEC	
				114-1049	
				SIZE CODE	
				DRAWING NO	
				SCALE 5:1	
				SHEET 1 OF 1	
				REV AE1	

STE TE Connectivity
OBSELETE NOT the LATEST REVISION