


## CUSTOMER DRAWING



Product Revision		Product Dimensions					Cable Dimensions			
Product Name		øA min	øB min	C min	L max	H ref	øE	øF min	M min	N max
D-155-0325	B	3.00 (0.118)	4.3 (0.170)	10 (0.400)	58.2 (2.290)	25 (0.985)	1.5 (0.060) to 3.00 (0.120)	1.5 (0.060)	8 (0.315)	28 (1.100)
D-155-0350	B				81 (3.200)	50 (1.970)				
D-155-0450	A	4.00 (0.157)	5.5 (0.216)	10 (0.400)	81 (3.200)	50 (1.970)	2.0 (0.080) to 3.80 (0.150)	2.0 (0.080)	12.5 (0.495)	60 (2.365)
D-155-0475	A				106 (4.175)	75 (2.955)			15 (0.590)	83 (3.270)
D-155-0550	A	5.00 (0.197)	6.5 (0.255)	10 (0.400)	81 (3.200)	50 (1.970)	2.5 (0.098) to 4.5 (0.177)	2.5 (0.098)	12.5 (0.495)	60 (2.365)
D-155-0575	A				106 (4.175)	75 (2.955)			15 (0.590)	83 (3.270)
D-155-0625	A	6.00 (0.236)	7.5 (0.295)	10 (0.400)	55 (2.216)	25 (0.985)	3.5 (0.137) to 5.5 (0.216)	3.5 (0.137)	8 (0.315)	28 (1.100)
D-155-0650	A				81 (3.200)	50 (1.970)			12.5 (0.495)	60 (2.365)
D-155-0675	A				106 (4.175)	75 (2.955)			15 (0.590)	83 (3.270)
D-155-0975	B	9.00 (0.355)	10.5 (0.413)	10 (0.400)	108 (4.250)	75 (2.955)	4.8 (0.190) to 9.0 (0.355)	4.8 (0.190)	15 (0.590)	83 (3.270)


### MATERIALS

- INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene fluoride.
- SHIELD: Solder impregnated, flux coated, tin plated copper braid.  
SOLDER: TYPE Sn63 per ANSI-J-STD-006.  
FLUX: TYPE ROM1 per ANSI-J-STD-004.
- MELTABLE RINGS: Thermally stabilized thermoplastic. Color: gray.

### APPLICATION

- These parts are designed to provide an environment protected in-line splice between the shield of cables, rated for 135°C minimum, meeting the dimensional criteria listed, having tin, silver or nickel plated copper shields.
- Temperature range: -55°C to +150°C. Install using Raychem-approved convection or infrared heating tools.

For best results, prepare the cable as shown:



\* A trademark of Raychem Corporation.

		<b>Raychem Devices</b>	TITLE: <b>SOLDERSHIELD* SPLICE</b>			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.			DOCUMENT NO.: <b>D-155-0XXX</b>			
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A  ROUGHNESS IN MICRON	Raychem reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.	ECO NUMBER:  ECO-17-002501	REPLACES: D15503XX, D15504XX, D15505XX, D15506XX, D15509XX		
DRAWN BY: M. FORONDA 9/20/2004	REV. DATE: 02/22/2017	PROD. REV. SEE TABLE	DOC REV: B	SCALE: None	SIZE: A	SHEET: 1 of 1

© 2017 TE CONNECTIVITY CORPORATION. ALL RIGHTS RESERVED.

If this document is printed it becomes uncontrolled. Check for the latest revision