





LOC	DIST	REVISIONS			
CM	00	P	LTR	DESCRIPTION	DATE
		G1		REVISED PER ECO-11-004917	21MAR11

1 AMP LOGO AND CAVITY NUMBER LOCATED ON EITHER SURFACE.




MATING CONNECTOR INTERFACE



TYPICAL PLUG CAVITY SECTION
<DIMENSIONS REFERENCE ONLY>

2.67	.105	5.08	.200	19.81	.780
2.13	.084	5.05	.199	11.18	.440
0.64	.025	3.68	.145	8.76	.345
0.25	.010	3.18	.125	8.64	.340
0.13	.005	2.79	.110	7.62	.300
MM	IN	MM	IN	MM	IN

CONVERSION TABLE



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± 0.13

4 PLC ± —

ANGLES ± —

FINISH —

MATERIAL:

NYLON, UL 94V-2

DWN L. McEACHIN, Sr. 30MAY00

CHK S. RIDGILL 30MAY00

APVD S. RIDGILL 30MAY00

NAME

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

SIZE A1

CAGE CODE 00779

DRAWING NO C=770340

RESTRICTED TO

BLACK 770340-3

NATURAL 770340-1

COLOR PART NO

TE Connectivity

PLUG, 2 CIRCUIT, .062 PIN AND SOCKET

SCALE 5:1

SHEET 1 OF 1

REV G1