


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E2	PART OBSOLESCENCE	20DEC2024	RS	VG

POS. PER ROW	L±0.4	PART NO.
-	-	-
2	5.08	2-3
3	7.62	3-3
4	10.16	4-2
5	12.70	5-2
6	15.24	6-2
7	17.78	829315 7-2
8	20.32	8-3
9	22.86	9-2
10	25.40	-1 0-3
11	27.94	1- -1
12	30.48	-1 2-2
13	33.02	-1 3-3
14	35.56	-1 4-2
15	38.10	-1 5-2
16	40.64	-1 6-3
17	43.18	-1 7-3
18	45.72	-1 8-2
19	48.26	-1 9-2
20	50.80	-2 0-3
21	53.34	-2 1-2
22	55.88	-2 2-2
23	58.42	-2 3-2
24	60.96	-2 4-2
25	63.50	-2 5-2
26	66.04	-2 6-2
27	68.58	-2 7-2
28	71.12	-2 8-2
29	73.66	-2 9-2
30	76.20	-3 0-2
31	78.74	-3 1-2
32	81.28	-3 2-2
33	83.82	-3 3-3
34	86.36	-3 4-2
35	88.90	-3 5-2
36	91.44	-3 6-2
37	93.98	-3 7-2
38	96.52	-3 8-2
39	99.06	-3 9-2
40	101.60	-4 0-2
41	104.14	-4 1-2
42	106.68	-4 2-2
43	109.22	-4 3-2
44	111.76	-4 4-2
45	114.30	-4 5-2
46	116.84	-4 6-2
47	119.38	-4 7-2
48	121.92	-4 8-2
49	124.46	-4 9-3
50	127.00	-5 829315 0-3



1 MATING SIDE: Min 0.76µm (PdNi + Au FLASH)IN ZONE "F"
OVER Min 1.27µm Ni
(Alternative plating – Min 0.76µm Au OVER Min 1.27µm Ni)
SOLDER SIDE: Min. 2.5µm TIN OVER Min 1.27µm Ni


2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI

3 OBSOLETE

CONTACT PIN	CuZn	1
PIN HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	SURFACE COLOR

TE Connectivity. All Rights Reserved.



DIMENSIONS:		DWN	28NOV1988		MATERIAL	-		FINISH	-		
mm		CHK	A.HO		TE Connectivity						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		M.Schaarschmidt									
		APVD									
±0.2 mm		-		NAME SPEZ. AMPMODU II STIFTLEISTE ZWEIREIHIG							
0 PLC ± -		PRODUCT SPEC									
1 PLC ± -		108-18012									
2 PLC ± -		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
3 PLC ± -		26µm PLATING UPDATE (PdNi+AuFLASH)		A4		00779		C-829315		-	
4 PLC ± -		WEIGHT		-		CUSTOMER DRAWING					
ANGLES ± NOTE 1 0.76µm		-									
						SCALE		4:1		SHEET	
								1		OF 1	
										REV	
										E2	