


REV. 0
DCO 143151

COIL: @ 25°C
 RESISTANCE 1350 OHMS ± 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 13.5 VDC
 MUST RELEASE 8.1 VDC MAX, 1.5 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 100 g's 11 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C
 NOTES: OPERATE & RELEASE 4 MS MAX.
BOUNCE 1.5 MS MAX.
DIELECTRIC 500 VAC - ALL POINTS

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: 2A 28VDC RES.
0.5A 28VDC IND. L/R .008 MAX., 0.5A
115VAC CASE UNGROUNDED, 125A 115VAC
CASE GROUNDED RES. 100,000 OPS

DR. BSH 08/14/01

CK. TLQ 8-14-01

CII Technologies
 advanced control electronic solutions

CUST. C.I.I. STD.
 CUST. NO. _____ REV. _____

"3SBC" RELAY

3SBC5008K1