

BAND (SUPPLIED FLAT) ③⑨
(SEE PART NUMBER BREAKDOWN
FOR OPTIONS)

CODE 54 - BANDING BACKSHELL

BNX54AB00-1608 -S

SERIES _____
BNX - BAND STRAP NOT INCLUDED
BND - BAND STRAP INCLUDED
(SEE BAND TERMINATION
CONFIGURATION)
CONNECTOR INTERFACE _____
MATERIAL _____
REFER TO CH00-0250-016
FINISH _____
REFER TO CH00-0250-016
ANGLE _____
ORDER NUMBER (TABLE 1) _____
ENTRY SIZE (TABLE 2) _____
BAND TERMINATION CONFIGURATION ③ ⑨ _____
V - ONE STEP STANDARD BAND
W - ONE STEP MICROBAND
U - TWO STEP STANDARD BAND
FOR BNX, LEAVE BLANK
OPTION FIELD SEPARATOR _____
MODIFICATION CODE _____
REFER TO CH00-0250-016 ②

NOTES:

1. THIS PRODUCT IS DESIGNED TO TERMINATE A BRAIDED CABLE SHIELD BY MEANS OF A BAND STRAP AND A HEAT SHRINKABLE LIPPED BOOT TO A CONNECTOR.

② FOR ADDITIONAL DIMENSIONS, ORDERING INFORMATION AND MODIFICATIONS, SEE CH00-0250-016.

③ SEE DRAWING BND-XXXXX FOR BAND STRAP OPTIONS, DIMENSIONS AND INFORMATION.

4. BACKSHELL TO BE PERMANENTLY MARKED WITH CODE IDENTIFICATION NUMBER AND FULL BASIC PART NUMBER (e.g. 06090-BND54AB00-1608). BACKSHELL TO BE MARKED WITH "BND" EVEN IF NO BAND IS ORDERED. THE BAND TERMINATION CONFIGURATION CODE IS FOR ORDERING INFORMATION ONLY AND IS NOT A PART MARKING REQUIREMENT.

⑤ ALL ENTRY SIZES ARE SHOWN IN TABLE 2. MAXIMUM ENTRY SIZES ARE SHOWN IN TABLE 1. FOR LARGER ENTRY SIZES, A 2 PIECE BACKSHELL ASSMEBLY (TYPE 2) IS SUPPLIED. SEE CH00-0250-016 FOR FURTHER DETAILS.


⑥ BACKSHELL MATES TO MIL-DTL-81703, SERIES III, MS3424, MS3446, MS3464, MS3467, MS3468.

⑦ BACKSHELL MATES TO MIL-C-5015G, MS3400 SERIES, CLASS D, E, K, L, U & W, MS3400, MS3401, MS3404, MS3406 MS3424, MS3446, MS3464, MS3467, MS3468, MS3450, MS3451, MS3454, MS3456, MS3470, MS3471, MS3472, MS3474, MS3475, MS3476. MIL-C-83723, SERIES II, CLASS A & L. MIL-C-83723, SERIES I & II, CLASS A, G, K, R & S: M83723/1, /2, /3, /4, /5, /6, /7, /8, /13, /14, /36, /37, /38, /39, /40, /41, /42, /43, /48, /49, /65, /66, /67, /68, /69, /70, /71, /72, /73, /74, /75, /76, /77, /78, /82, /83, /84, /85, /86, /87, /91, /92, /95, /97, /98, (MS3155 CONTROLLED INTERFACE).









⑧ THESE DIMENSIONS APPLY IF A SELF-LOCKING COUPLING NUT IS USED.

⑨ V AND U BANDS ARE SUITABLE FOR ENTRY SIZES 03-24, W IS SUITABLE FOR ENTRY SIZES 03-12 ONLY. CONTACT FACTORY FOR BAND OPTIONS ON LARGER ENTRY SIZES.

DRAWN	K.WINCZURA	DATE	01/12/2014	 3RD ANGLE PROJECTION NOT TO SCALE	TITLE: BANDING BACKSHELL	 Polamco			
CHECKED		01/12/2014							
APPROVED	K.SHEPPARD	04/12/2014	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°		ASSY USED ON: MIL-DTL-26482 SERIES II / MIL-DTL-83723 SERIES I & III				
APPROVED	H.SMITH	17/09/2015							
REVISIONS					TE CONNECTIVITY - POLAMCO LTD RESERVES THE RIGHT TO AMEND THIS DRAWING AND THE INFORMATION SET FORTH HEREON AT ANY TIME. USERS SHOULD INDEPENDENTLY EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.		DRAWING NO: BND54	DRAWING REV: PE	SHT 1
LTR	DESCRIPTION		DATE	APPROVED					
PD	REVISED PER ECO-15-013261		17/09/2015	H.SMITH					
PE	REVISED PER ECO-15-016545		17/11/2015	H.SMITH					
TE CAGE CODE: 06090 POLAMCO/TE CAGE CODE: U5792									



STAINLESS
STEEL
TEETH VIEW



DRAWN	K.WINCZURA	DATE	01/12/2014
CHECKED		DATE	01/12/2014
APPROVED	K.SHEPPARD	DATE	04/12/2014
APPROVED	H.SMITH	DATE	17/09/2015
REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
PD	REVISED PER ECO-15-013261	17/09/2015	H.SMITH
PE	REVISED PER ECO-15-016545	17/11/2015	H.SMITH
TE CAGE CODE: 06090 POLAMCO/TE CAGE CODE: U5792			

TITLE:			BANDING BACKSHELL		
ASSY USED ON:			MIL-DTL-26482 SERIES II / MIL-DTL-83723 SERIES I & III		
TE CONNECTIVITY - POLAMCO LTD RESERVES THE RIGHT TO AMEND THIS DRAWING AND THE INFORMATION SET FORTH HEREON AT ANY TIME. USERS SHOULD INDEPENDENTLY EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.			DRAWING NO: BND54		DRAWING NO: PE

 Polamco  TE connectivity			
DRAWING NO:	DRAWING REV:	SHT	
BND54	PE	2	

MODIFICATION S (SELF-LOCKING COUPLING NUT)




TABLE 1

ORDER NO.	SHELL SIZE		A THREAD	ØB MAX	ØB MAX (8)	MAX ENTRY	C ±0,5	D ±0,5	W ±0,5	T ±0,5	E ±0,5	THESE DIMENSIONS APPLY IF BACKSHELL IS STAINLESS STEEL OR NICKEL ALUMINIUM BRONZE		
	(6)	(7)										W ±0,5	T ±0,5	E ±0,5
08		8 & 8S	1/2-20 UNF	15,6	18,0	04	16,6	25,1	24,5	17,5	30,0	22,4	17,5	29,0
10		10, 10S, 10SL	5/8-24 UNEF	18,6	21,0	06	16,8	26,2	26,5	17,8	32,0	25,0	18,8	30,3
12	7	12 & 12S	3/4-20 UNEF	21,7	25,0	08	17,3	26,6	29,0	18,7	33,5	28,3	20,4	31,9
14	12	14 & 14S	7/8-20 UNEF	24,9	28,0	09	18,1	27,5	30,5	19,0	35,4	30,4	21,5	33,0
16	19	16 & 16S	1-20 UNEF	28,2	31,0	11	19,0	28,3	34,0	21,0	36,7	33,5	23,0	34,5
18	27	18	1 1/16-18 UNEF	30,9	34,0	12	19,2	28,8	37,0	23,5	36,7	35,5	24,0	35,5
20	37	20	1 3/16-18 UNEF	34,1	36,5	14	20,1	29,7	42,0	27,0	38,3	38,8	25,7	37,2
22		22	1 5/16-18 UNEF	37,3	39,8	16	20,3	30,0	44,0	27,0	40,0	41,9	27,2	38,7
24		24	1 7/16-18 UNEF	40,4	42,0	18	21,8	30,9	45,0	27,0	41,6	44,8	28,7	40,2
28		28	1 3/4-18UNS	50,0	49,8	22	23,3	31,6	54,2	31,4	45,3	50,7	31,6	43,2
32		32	2-18 UNS	56,3	57,2	26	25,0	33,2	60,9	36,4	48,1	60,0	33,5	46,0
36		36	2 1/4-16 UN	62,7	63,6	28	26,2	34,4	67,2	38,0	51,3	65,5	36,0	51,3
40		40	2 1/2-16 UN	69,0	70,0	32	28,6	35,7	73,2	41,0	54,3	72,0	39,3	54,3
44		44	2 3/4-16 UN	75,4	75,4	34	30,1	37,3	79,5	44,1	57,5	75,5	40,8	57,5
48		48	3-16UN	81,7	81,7	34	31,3	38,5	85,8	47,2	60,6	75,5	40,8	60,6
61	61		1 1/2-18 UNEF	42,0	43,6	18	22,1	30,9	47,8	28,0	43,0	48,3	27,0	43,1

TABLE 2

ENTRY SIZE	ØZ MIN	ØS MAX	ØY MAX	ØK MAX	ØK MAX (8)	F ±0,5	G ±0,5	H ±0,5	M ±0,5	J ±0,5	THESE DIMENSIONS APPLY IF BACKSHELL IS STAINLESS STEEL OR NICKEL ALUMINIUM BRONZE		
											H ±0,5	M ±0,5	J ±0,5
03	4,7	7,8	14,0	NA	NA	NA	NA	NA	NA	NA	NA	NA	NA
04	6,3	9,4	14,0	NA	NA	NA	NA	NA	NA	NA	NA	NA	NA
05	7,9	11,0	15,5	21,0	24,6	12,5	26,2	24,0	15,5	32,0	24,3	17,2	31,2
06	9,5	12,5	17,2	21,0	24,6	12,5	26,2	24,0	15,5	32,0	24,3	17,2	31,2
07	11,1	14,1	18,7	21,0	24,6	12,5	26,2	24,0	15,5	32,0	24,3	17,2	31,2
08	12,7	15,7	20,3	24,5	28,3	13,1	26,6	27,0	17,0	33,5	28,3	19,4	33,0
09	14,2	17,3	21,9	24,5	28,3	13,1	26,6	27,0	17,0	33,5	28,3	19,4	33,0
10	15,8	18,8	23,5	29,0	32,4	13,5	27,5	31,0	19,5	35,4	31,1	21,0	34,9
11	17,4	20,5	25,1	32,5	35,6	14,5	28,3	34,0	21,0	36,7	34,2	22,8	35,5
12	19,0	22,0	26,7	32,5	35,6	14,5	28,3	34,0	21,0	36,7	34,2	22,8	35,5
13	20,6	23,6	28,3	35,5	38,5	15,5	28,8	35,0	20,0	38,3	38,5	25,3	37,2
14	22,2	25,2	29,9	35,5	38,5	15,5	28,8	35,0	20,0	38,3	38,5	25,3	37,2
15	23,8	26,8	31,5	37,0	41,7	16,1	29,7	38,0	21,5	40,0	40,7	26,1	38,7
16	25,4	28,4	33,1	37,0	41,7	16,1	29,7	38,0	21,5	40,0	40,7	26,1	38,7
18	28,6	30,0	36,3	40,0	43,9	16,5	30,0	42,0	24,0	41,6	43,7	27,6	40,2
20	31,8	34,8	39,5	43,5	47,0	17,0	30,9	45,0	25,5	43,0	46,4	29,1	44,9
22	35,0	38,0	42,7	48,5	50,0	18,5	31,3	54,5	31,0	45,1	50,0	31,0	45,1
24	38,1	41,1	45,9	52,1	56,0	21,9	32,8	58,0	33,0	51,1	53,5	33,0	51,1
26 (9)	41,3	44,3	49,1	56,6	61,3	25,7	32,8	62,5	35,0	51,1	58,0	35,0	51,1
28 (9)	44,5	47,5	52,3	63,0	64,5	26,9	33,8	65,5	34,5	54,1	61,0	34,5	54,1
30 (9)	47,6	50,7	55,6	75,5	80,2	29,2	34,4	69,0	36,0	57,4	64,5	36,0	57,4
32 (9)	50,8	53,8	58,5	75,5	80,2	29,2	34,4	72,0	37,5	57,4	67,5	37,5	57,4
34 (9)	54,0	57,0	61,8	75,5	80,2	29,2	34,4	75,5	39,0	57,4	71,0	39,0	57,4

DRAWN	K.WINCZURA	DATE	01/12/2014	 3RD ANGLE PROJECTION NOT TO SCALE	TITLE: BANDING BACKSHELL	 Polamco
CHECKED		01/12/2014				
APPROVED	K.SHEPPARD	04/12/2014	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°		ASSY USED ON: MIL-DTL-26482 SERIES II / MIL-DTL-83723 SERIES I & III	
APPROVED	H.SMITH	17/09/2015				
REVISIONS						
LTR	DESCRIPTION		DATE	APPROVED		
PD	REVISED PER ECO-15-013261		17/09/2015	H.SMITH		
PE	REVISED PER ECO-15-016545		17/11/2015	H.SMITH		
TE CAGE CODE: 06090 POLAMCO/TE CAGE CODE: U5792					TE CONNECTIVITY - POLAMCO LTD RESERVES THE RIGHT TO AMEND THIS DRAWING AND THE INFORMATION SET FORTH HEREON AT ANY TIME. USERS SHOULD INDEPENDENTLY EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.	DRAWING NO: BND54
						DRAWING REV: PE
						SHT 3