

# **HF6 Relay**

### Y-Design

- Frequency range DC to 6GHz
- Impedance 50Ω
- Small dimensions (16x7.6x10mm)
- 1 form C contact (1 changeover contact)
- Immersion cleanable
- Low power consumption (≤140mW)

Typical applications

Measurement and test equipment ATE, wireless base stations and antennas, wireless infrastructure, RF power amplifier

#### **Contact Data**

**Coil Data** 

Coil

51

52

53

54

55

56

57

Coil

71

72

73 74

75

76

77

code

code

Coil voltage range

Rated

voltage

VDC

З

4.5

5

6

9

12

24

Contact Data (continued)

Rated

voltage

VDC

З

4.5

5

6

9

12

24

50Ω version, Bistable, 1 coil

Coil versions, bistable

Coil versions, 50 version, monostable

Operate

voltage

**VDC**<sub>min</sub>

2.25

3.38

3.75

4.50

6.75

9.00

18.00

Set

voltage

VDC

2.25

3.38

3.75

4.50

6.75

9.00

18.00

1 form C, 1 CO
220VDC, 250VAC
2A
2A
60W, 62.5VA,
50W (2.5GHz)
50W (2.5GHz)
Ag, Au covered
100µV
<100mΩ at 10mA/30mV
typ. 3ms, max. 5ms
typ. 2ms, max. 5ms
typ. 4ms, max. 6ms
typ. 1ms, max. 3ms
20ms
10 <sup>7</sup> operations

Limiting

voltage

**VDC**<sub>max</sub>

6.50

9.80

10.90

13.00

19.60

26.10

52.30

Limiting

voltage

VDC

9.20

13.85

15.30

18.50

27.70


37.00


74.00

All figures are given for coil without pre-energization, at ambient temperature +23°C.

Contact Data (continued)									
50Ω version, bistable, 2 coils									
91	3	2.25	6.50	2.25	64	140			
92	4.5	3.38	9.80	3.38	145	140			
93	5	3.75	10.90	3.75	178	140			
94	6	4.50	13.00	4.50	257	140			
95	9	6.75	19.60	6.75	574	140			
96	12	9.00	26.10	9.00	1028	140			
97	24	18.00	52.30	18.00	2880	200			

All figures are given for coil without pre-energization, at ambient temperature +23°C.





10-2021, Rev. 1021 www.te.com © 2015 Tyco Electronics Corporation, a TE Connectivity Ltd. company

Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.

3 to 24VDC

Coil

resistance

Ω±10%

64

145

178

257

574

1028

4114

Coil

resistance

Ω±10%

128

289

357

514

1157

2057

8228

Rated coil

power

mW

140

140

140

140

140

140

140

Rated coil

power

mW

70

70

70

70

70

70

70

Release

voltage

**VDC**<sub>min</sub>

0.30

0.45

0.50

0.60

0.90

1.20

2.40

Reset

voltage

VDC

-2.25

-3.38

-3.75

-4.50

-6.75

-9.00

-18.00

Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.

1

(

#### **Coil operating Range**




# HF6 Relay (Continued)

Insulation Data			
Initial dielectric strength			
between open contacts	600Vrms		
between contact and coil	1000Vrms		
Initial surge withstand voltage	1000 41110		
between open contacts	1000V		
between contact and coil	1500V		
	1000		
DE Data			
RF Data Isolation at 900MHz/3GHz/6GHz	80dB/60dB/30dB		
Insertion loss at 900MHz/3GHz/6GHz	0.05dB/0.15dB/0.80dB		
Voltage standing wave ratio (VSWR)			
at 900MHz/3GHz/6GHz	1.05/1.10/1.40		
Typical RF performance, 50Ω version	ION		
°			
-10			
-20			
-30			
-40			
50			
90 tisee			
-1000 L	4 5 6		
	ON LOSS		
·			
-0.5			
[8]	i)		
273 (19)			
-1			
	······		
-1.5	4 5 6 CHz]		
VS	WR		
1.50	NC		
1.45			
1.40			
1.35			
1.30			
¥ 1.25	/		
1 20	/		
1.15			
1.10	and the second s		
1.10 1.05			
1.10			

# Terminal assignment

TOP view on component side of PCB Monostable



10-2021, Rev. 1021 www.te.com © 2015 Tyco Electronics Corporation, a TE Connectivity Ltd. company

2

Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.

Ē

Bistable, 1 coil

22

Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at <a href="http://relays.te.com/definitions">http://relays.te.com/definitions</a>

Contacts are shown in reset condition.

Contact position might change during transportation and must be reset before use.

10 11

reset 🕂

+ set

- set + Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.

+ reset

reset 🕂


<u>\_\_\_</u> 15 14 13 12 | | | | | |

#### **Other Data**

Other Data				
	V, China RoHS, REACH, Halogen content			
refer to th	ne Product Compliance Support Center at			
www.te.com/customersupport/rohssupportcente				
Ambient temperature	-55°C to +85°C			
Thermal resistance	<165K/W			
Category of environmental protect	ion			
IEC 61810	RT III - wash tight			
Degree of protection, IEC 60529	IP 67, immersion cleanable			
Vibration resistance (functional)	35g, 10 to 1000Hz			
Shock resistance (functional), half	sinus 11ms 50g			
Shock resistance (destructive), hal	If sinus 0.5ms 150g			
Terminal type	SMT			
Weight	max. 3g			
Resistance to soldering heat	Peak value			
SMT IEC 60068-2-58	250°C/10s			
Moisture sensitive level, JEDEC J-	Std-020D MSL3			
Ultrasonic cleaning	not recommended			
Packaging/unit, SMT	reel/400 pcs., box/400 pcs. or 2000 pcs.			

## PCB layout

TOP view on component side of PCB



Bistable, 2 coils

\_[





14.9-0.1

16-0.5

5.08-0.1

HF6 xx

zzV DC

1.27-0.

5.08+0.1

6.35-0.15

Ų

# HF6 Relay (Continued)

#### Dimensions

τu

3.81.0

2.54+0


0.8

0.8


1.1


8.6.05






# Packing







10-2021, Rev. 1021 www.te.com © 2015 Tyco Electronics Corporation, a TE Connectivity Ltd. company

Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section. Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.

3



**RF Signal Relays** 

## HF6 Relay (Continued)

# Product code structure Typical product code HF6 53 Type HF6 High Frequency Relays HF6 Series 1 form C, 1 CO Image: Coll code: please refer to coil versions table Image: Coll code: please refer to coil versions table Image: Coll code: please refer to coil versions table Image: Coll code: please refer to coil versions table Image: Coll code: please refer to coil version, monostable 1 coil Image: Coll code: please refer to coil version, monostable 1 coil Image: Coll code: please refer to coil version, monostable 1 coil Image: Coll code: please refer to coil version, bistable 1 coil Image: Coll code: please refer to coil version, bistable 1 coil Image: Coll code: please refer to coil version, bistable 1 coil Image: Coll code: please refer to coil version, bistable 1 coil Image: Coll code: please refer to coil version, bistable 1 coil Image: Coll code: please refer to coil version, bistable 1 coil Image: Coll code: please refer to coil version, bistable 1 coil Image: Coll code: please refer to coil version, bistable 1 coil Image: Coll code: please refer to coil version, bistable 1 coil Image: Coll code: please refer to coil version, bistable 2 coils Image: Coll code: please refer to coil version, bistable 2 coils Image: Coll code: please refer to coil version, bistable 2 coils Image: Coll code: please refer to coil version, bistable 2 coils Image: Coll code: please refer to coil version, bistable 2 coils Image: Coll code: please refer to coll version, bistable 2 coils Image: Coll code: please refer to coll version, bistable 2 coils Image: Coll code: please refer to coll version, bistable 2 coils

Product code	Arrangement	Version	Coil	Coil type	Part number
HF6 51	1 form C (1 CO)	50ohm	3VDC	Monostable	1462052-1
HF6 53			5VDC		1462052-3
HF6 56			12VDC		1462052-6
HF6-73	1. tarm C (1 CO)	500hm	5VDC	Bistable 1.coil	1-1462052-0
HF6 93	1 form C (1 CO)	50ohm	5VDC	Bistable 2 coils	1-1462052-7
HF6-96			12VDC		2-1462052-0

This list represents the most common types and does not show all variants covered by this data sheet. Other types on request

4