


THIS DRAWING IS UNPUBLISHED.
VERTRAULICHE UNVEROEFFENTLICHTE ZEICHNUNG.
RELEASED FOR PUBLICATION
FREI FUER VEROEFFENTLICHUNG
COPYRIGHT 1999 BY AMP INCORPORATED.
ALL RIGHTS RESERVED.
ALLE RECHTE VORBEHALTEN.

MATED WITH: PASSEND ZU: 2-964294-1		LOC AI	DIST —	REVISIONS AENDERUNGEN DESCRIPTION BESCHREIBUNG					DATE	DWN	APVD
PROJECT NR.: B916106				P	LTR				02-MAR-99	SCHÄFER	—
					A1	NEW DRAWING PUBLISHED					
REFER TO PRODUCT GROUP DRAWING 1241437 FOR LATEST INFORMATION ON THE PART											
—		—		—		—		—		—	
CUSTOMER PART NO		AMP PART NO		REV.	PCS.	MATERIAL		SURFACE COLOR	DESCRIPTION		
DIMENSIONS: DIMENSIONEN: mm		DWN R. Schäfer		16JUN1999		MATERIAL —		FINISH OBERFLAECHE/FARBE —			
TOLERANCES UNLESS OTHERWISE SPECIFIED, ALLGEMEINTOLERANZEN p.p. ISO 8015 p.p. ISO 2768 - mH -E p.p. DIN 16901 - 140		CHK —		—		AMP		AMP Deutschland GmbH D - 63225 Langen			
p.p. ISO 2768 - mH -E p.p. DIN 16901 - 140		APVD —		—		NAME PART-NO. CROSS-REFERENCE INFO Teile-Nr. Zuweisungs-Information					
p.p. ISO 2768 - mH -E p.p. DIN 16901 - 140		PRODUCT SPEC PRODUKTSPEZ. —		—		SIZE A4		CAGE CODE 00779		DRAWING NO ZEICHNUNGS-NR. C-1241389	
p.p. ISO 2768 - mH -E p.p. DIN 16901 - 140		APPLICATION SPEC VERARBEITUNGSSPEZ. —		—		RESTRICTED TO NUR FUER —					
ANGLES/WINKEL ±—		WEIGHT GEWICHT —		—							
		CUSTOMER DRAWING		/KUNDENZEICHNUNG		MASSSTAB —		BLATT 1 OF VON 1		A1	