








LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			D1	REVISED (ECR-16-017989)	21DEC2016	SJ	JW
			D2	REVISED (ECR-20-018098)	24DEC2020	HC	YJ
			E	REVISED (ECR-23-190293)	20FEB2024	CH	YH



SECTION B-B
SCALE 2:1



SECTION A-A
SCALE 2:1



		-	-	
964273-I	1.0~2.5	PRETINNED	963292-I	D2 828922-I
964286-I	0.5~1.0	PRETINNED	963293-I	
964282-I	0.35~0.5	PRETINNED	963294-I	
TE ORDER NO STRIP FORM	WIRE RANGE MM	FINISH	SINGLE WIRE SEAL NO	SEALING PLUG
RECOMMENDED CONTACT SYSTEM: JPT -TYPE A ; SEALED				

-	-	-	-	
969044-I	2.5~4.0	PRETINNED	963245-I	
969042-I	1.0~2.5	PRETINNED	963244-I	(D2) 100132-I
969040-I	0.5~1.0	PRETINNED	963243-I	
TE ORDER NO STRIP FORM	WIRE RANGE MM	FINISH	SINGLE WIRE SEAL NO	SEALING PLUG
RECOMMENDED CONTACT SYSTEM: SPT -TYPE A ; SEALED				

2098165-1	0.3~0.5	PRETINNED	2005423-3 2109258-4
TE ORDER NO	WIRE RANGE MM	FINISH	SEALING PLUG
RECOMMENDED CONTACT SYSTEM: 0.8X0.64			

NOTE.

1. APPLICABLE COVER ASSY : TE P/N 2005243
- (D1) 2. APPLICABLE CAVITY PLUG : TE P/N 2005423-3, 2109258-4 FOR 025 TERMINAL
- (D2) 3. APPLICABLE SEALING PLUG : TE P/N 828922-1 FOR 110 TERMINAL
TE P/N 100132-1 FOR 250 TERMINAL
- (E) 4. GENERAL TOLERANCE : ± 0.5 , ANGLE $\pm 3^\circ$

					D				
58-4 FOR 025 TERMINAL					ASS'Y P/N	3-2005238-4	2-2005238-3	1-2005238-2	2005238-1
0 TERMINAL									
0 TERMINAL									
6	PINK	PBT-GF30	SEAL COVER	I					
	GRAY				I				
	BLACK					I			
	NATURAL						I		
5	RED ORANGE	SILICONE	FAMILY SEAL	I	I	I	I		
C	4	BROWN	SILICONE (LSR)	INNER SEAL	I	I	I	I	
	3	NATURAL	PBT-GF30	DBL HSG	I	I	I	I	
	2	BLACK	PA6-GB20/GF10	CARRIER HSG	I	I	I	I	
E	1	BLACK	PA66-GF35	PLUG HSG	I	I	I	I	
	NO	COLOR	MATERIAL	DESCRIPTION	Q'TY				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SJ CH01 CHK SJ CH01 APVD JW JUNG PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		NAME 025/110/250 HYBRID 38P ISL PLUG ASSY	
MATERIAL -		CUSTOMER DRAWING;RESTRICTED CUSTOMER		SIZE A2	
		CAGE CODE 00779		DRAWING NO C=2005238	
		RESTRICTED TO -		SCALE :	
		SHEET 1 OF 2		REV E	

