
CUSTOMER DRAWING



	Product Dimensions					Cable Dimensions		
Product Name	Ident.	L±1.75	Ø B	ØС	Н	ØΕ	ØF	Ø D
	Code	(L±0.07)	min.	min.	min.	max.	min.	max.
S03-06-R-100HN	S0306R	16.5	1.90	2.67	8.20	2.67	0.90	1.90
		(0.650)	(0.075)	(0.105)	(0.323)	(0.105)	(0.035)	(0.075)
S03-07-R-100HN	S0307R	16.5	2.67	3.68	8.20	3.68	1.40	2.67
		(0.650)	(0.105)	(0.145)	(0.323)	(0.145)	(0.055)	(0.105)
S03-08-R-100HN	S0308R	16.5	4.32	5.08	8.20	5.08	2.15	4.32
		(0.650)	(0.170)	(0.200)	(0.323)	(0.195)	(0.085)	(0.170)
S03-09-R-100HN	S0309R	19.1	5.97	6.48	8.20	6.48	3.30	5.97
		(0.750)	(0.235)	(0.255)	(0.323)	(0.255)	(0.130)	(0.235)
S03-10-R-100HN	S0310R	19.1	6.98	7.62	8.20	7.62	4.30	6.98
		(0.750)	(0.275)	(0.300)	(0.323)	(0.300)	(0.170)	(0.275)

MATERIALS

- 1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene fluoride.
- 2. SOLDER PREFORM WITH FLUX AND THERMAL INDICATOR:

SOLDER: TYPE Sn63 per ANSI-J-STD-006.

FLUX: TYPE ROL1 per ANSI-J-STD-004.


THERMAL INDICATOR: Color change violet to colorless.

- 3. MELTABLE RINGS: Stabilized thermoplastic. Color: blue.
- 4. PRE-INSTALLED BRAID: Nickel plated copper strands per ASTM B355 Class 7. CMA 640.

APPLICATION

- 1. These parts are designed to provide an environment protected shield termination on cables, rated for 125°C minimum, meeting the dimensional criteria listed and having tin or silver plated shields and insulation compatible with the insert material. For compatible insulations, see MIL-S-83519/2 or consult TE Connectivity.
- 2. When installed per Raychem process standard RCPS-100-70, assemblies will meet those requirements of Raychem Specification RT-1404 and MIL-S-83519/2 which do not require electrical testing while parts are immersed in water.
- 3. Temperature range: -55°C to +150°C.
- 4. Parts shall be marked with identification code per table.

For best results, prepare the cable as shown:



= TE				Raychem THERMOFIT DEVICES THERMOFIT SOLDERSLEEVE* DEVICE SHIELD TERMINATION WITH BRA					
	Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets] TOLERANCES: ANGLES: N/A TE Connectivity reserves the right to				DOCUMENT NO.: S03-XX-R-100HN				
0.00 N/A 0.0 N/A 0 N/A		HNESS IN	amend this drawing at any time. Users should evaluate the suitability of the product for their application.		REV:		DATE: 30-Mar-2020		
DRAWN BY: M. FORONI	DA	DATE: 12/03/9	9	ECO: ECO-20-004510	SCALE: NTS		SIZE: A	SHEET: 1 of 1	

 $\ensuremath{\mathbb{C}}$ 2020 TE Connectivity Ltd. Family of Companies. All Rights Reserved.

If this document is printed it becomes uncontrolled. Check for the latest revision.

^{*}TE Connectivity, TE connectivity (logo), Raychem, THERMOFIT, SolderSleeve are trademarks