

# STRADA WHISPER Backplane Connectors

### **Blinding Speeds**

The STRADA Whisper backplane family was designed with your end customer's need for high-performing, high-bandwidth systems in mind. Its revolutionary design transfers data at blinding speeds of 56 Gbps and offers unparalleled scalability up to 112 Gbps—allowing you to achieve efficient future system upgrades without costly backplane or midplane redesigns.

### Performance Matters

The STRADA Whisper product family operates with extremely low noise, low insertion loss and little to no skew—all of which provide system architects with design flexibility and high design margin. Specific versions are available for 100-Ohm and 85-Ohm applications so you don't have to compromise on total system impedance design.


Mechanically, the STRADA Whisper connector family mirrors most high-speed backplane connectors in the market for easy implementation. It differentiates itself through folded signal pins surrounded by strong, protective C-shaped shields, which make the product family one of the most robust offerings in the market. Additionally, the connector footprint keeps crosstalk down and the overall connector design uses latest eye-of-needle (EON) technology.

### Your Design Partner For 112 Gbps Architectures

To ensure smooth transitions from 10 Gbps to 112 Gbps systems using the STRADA Whisper connector, TE Connectivity (TE) can assign a team of experts—comprised of our best signal integrity and mechanical engineers—to help you develop a solution that fits right into your architecture. Whether it's traditional backplane, orthogonal midplane, direct plug orthogonal, or a cabled-backplane system, TE can tailor the STRADA Whisper product portfolio to best fit and enable your system architecture.

# **Applications**

- Servers & Storage
- Switches
- Routers
- Optical Transport




**Orthogonal Midplane** 

Cabled-Midplane

**Direct Plug Orthogonal** 

### **Electrical Specifications**

- Power Sum FEXT is lower than -50 dB for system implementation at 12.5 GHz
- Insertion loss is less than 1dB and linear up to 20 GHz
- Individual shielded pairs offer excellent signal integrity / EMI performance
- Little to no skew through high-speed differential pairs
- Common mode impedance controlled throughout the connector, including footprint and mating interface
- Superior 25-Gbps electrical performance maintained even in a 1.5mm unmated condition
- No reliance on noise cancellation, unlike some competitive products, which can be critical in high-speed applications and the presence of uncontrollable system skew
- 85-Ohm and 100-Ohm versions available



### **PRODUCT OFFERINGS**

TE offers the STRADA Whisper product family in multiple versions: standard, orthogonal (for mid-plane structures), direct plug orthogonal (DPO) and a cabled version that allows you to run longer distances with lower insertion loss than PCB materials.

- Backplane Configuration
- » 4.5mm right-angle receptacle
- » 4.5mm vertical header
- » 3.9m right-angle receptacle
- » 3.9mm vertical header
- Orthogonal Midplane configuration
- » 3.9mm orthogonal right-angle receptacle
- » 3.9mm orthogonal header
- DPO Configuration
- » 3.9mm DPO connector
- » 3.9mm orthogonal right angle receptacle
- Cable Assemblies
- » 3.9mm cable assembly
- » 3.9mm right angle cable assembly

4.5mm products are offered in 100-Ohm and 3.9mm configurations are offered in 85- and 100-Ohm versions.

Support Tools: S-parameter Models Routing Designs Application Instructions


Related Links: Whitepaper

### Mechanical

# RECEPTACLE HEADER ASSEMBLY

### **DPO ASSEMBLY**

### **CABLE ASSEMBLY**



# Six ground connection points





Fig. 1. Close up of signal contacts

Connector allows for 1.5mm worth of mating separation (between both the ground and signal) through TE's patented C-shaped, 360-grounding design, which includes an extra "orphan" shield at the bottom of the horizontal stack of contacts for complete shielding. The 360-ground shield provides high signal integrity margin, (electrical margin) granting you more chip and PCB flexibility.

C-shaped shields protrude outwards to protect signal pins from damage.

Signal contacts are arranged horizontally in highspeed differential pairs for zero skew. This makes your board design simpler, while increasing signal integrity performance and saving board space. Each differential pair is surrounded by six ground connection points.



Tabs on the sides of C-shield assure that ground contacts have at least a 2.5mm wipe, which helps maintain electrical

performance with 1.5mm of unmate condition.



# STRADA WHISPER BACKPLANE CONNECTORS

# For More Information

www.te.com/products/stradawhisper

# TE Technical Support Center

USA: +1 (800) 522-6752 +1 (905) 475-6222 Canada: Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

### te.com

STRADA Whisper, TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2018 TE Connectivity Ltd. family of companies All Rights Reserved.

6-1773465-0 05/18 DND

