




REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN APVD
H		REV PER ECO 16-004482	9-21-18	CT MS

1. QUALITY CONFORMANCE INSPECTION PER MIL-C-55302 (GROUP A, B & C).
2. PACKAGED PER MIL-C-55302
3. THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY, NOT TO CONTACT LOCATIONS.
4. SLOT OPTIONAL AT INDICATED AREA OF HOUSING.
5. CONTACTS: GOLD FLASH OVER 0.00127[.000050] NICKEL ENTIRE CONTACT, 0.00127[.000050] GOLD ON CONTACT AREA ONLY.
6. TOLERANCE TO CENTER OR RADIUS IS ± 0.15 [.006], TO END OF BLOCK ± 0.51 [.020].
7. MARKED IN APPROXIMATE AREA SHOWN
 EXAMPLE: AMP PART NO
 DATE CODE MILITARY PART NUMBER
8. CHARACTERS MARKED IN AREA SHOWN, EVERY FIFTH POSITION MARKED WITH A BAR
9. "CSA" LOGO MARKED ON HOUSING.



RECOMMENDED PC BOARD HOLE LAYOUT

M55302/128-CA2C	133.55 [5.258]	49	100	1-102195-0
MILITARY PART NUMBER	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. GALLUCCI BG 5-1-91	TE Connectivity																		
DIMENSIONS: INCHES		OK R. BENDORF	NAME																		
<table border="1"> <tr> <th>PLC</th> <th>TOLERANCES UNLESS OTHERWISE SPECIFIED:</th> <th>FINISH</th> </tr> <tr> <td>0</td> <td>±</td> <td>-</td> </tr> <tr> <td>1</td> <td>±</td> <td>-</td> </tr> <tr> <td>2</td> <td>±</td> <td>0</td> </tr> <tr> <td>3</td> <td>±</td> <td>0.25(.010)</td> </tr> <tr> <td>4</td> <td>±</td> <td>-</td> </tr> </table>		PLC	TOLERANCES UNLESS OTHERWISE SPECIFIED:	FINISH	0	±	-	1	±	-	2	±	0	3	±	0.25(.010)	4	±	-	PRODUCT SPEC	
PLC	TOLERANCES UNLESS OTHERWISE SPECIFIED:	FINISH																			
0	±	-																			
1	±	-																			
2	±	0																			
3	±	0.25(.010)																			
4	±	-																			
MATERIAL HOUSING:		APPLICATION SPEC																			
WEIGHT 0.000000		SIZE CAGE CODE DRAWING NO RESTRICTED TO																			
CUSTOMER DRAWING		SCALE 5:1 SHEET 1 OF 1 REV H																			