




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D1		REVISED PER ECR-23-194049	25MAR2024	RK	CAS



- 1 DIMENSIONS APPLY FROM THE BASIC DIMENSION LINE TO THE SURFACE INDICATED
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR: BLACK
- 4 GOLD PL 0.00076[.000030] ON CONTACT AREA BRIGHT TIN-LEAD PL 0.00254-0.00508[.000100-.000200] ON SOLDER TAIL ALL OVER NICKEL 0.00127[.000050]
- 5 GOLD PL 0.00076[.000030] ON CONTACT AREA MATTE TIN 0.00254-0.00508[.000100-.000200] ON SOLDER TAIL ALL OVER NICKEL 0.00127[.000050]



RECOMMENDED HOLE LAYOUT

PLATING	ROW Z	POSTS OMITTED	ROW Y	C	B	A	NO OF POS	AMP PART NUMBER
5	2,4,6,8,10,12,14,16,18, & 20		1,3,5,7,9,11,13,15,17, & 19	74.52 [2.934]	72.39 [2.850]	19	40	5-103856-1
4	2,4,6,8,10,12,14,16,18, & 20		1,3,5,7,9,11,13,15,17, & 19	74.52 [2.934]	72.39 [2.850]	19	40	103856-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	DK_SCHRUM	02APR98	
CHK	DL_SIMPSON	03APR98	
APVD	DL_SIMPSON	03APR98	
PRODUCT SPEC			
MATERIAL	SEE TABLE		ASSEMBLY, MOD II, HEADER, DBL ROW, .150 x .150 C/L, RIGHT ANGLE, SELECTIVELY LOADED
CUSTOMER DRAWING		SCALE	4:1
		SHEET	1 OF 1
		REV	D1