

# SCHRACK SRL7

## FORCE GUIDED RELAY

### INTRODUCTION

The flattest version of TE Connectivity (TE)'s Force Guided Relays with only 10.8 mm height for loads up to 6 A. The SCHRACK SRL7 family offers a 7-pole contact arrangement with a 5 NO (form A) + 2 NC (form B) contact set with force guided contacts according to IEC 61810-3. With an overall height of only 10.8 mm TE's SRL7 relay belongs to the flattest Force Guided Relays available. The low profile is highly reliable for the realization of compact safety modules (overall width of only 17.5 mm), but also whenever there is little space for installation height. The low coil power consumption of only 700 mW reduces heat dissipation and enables to increase and expand the usage of this relay from usual 70°C now up to 85°C ambient temperature conditions.



### FEATURES

- Low profile relay with force guided contacts according to EN 50205
- 5 form A (NO) + 2 form B (NC) contacts
- Reinforced insulation between contact circuits

### APPLICATIONS

- Emergency stop or two hand guard safety relays
- Expansion I/O modules
- Safety control circuits

### APPROVALS

- VDE Cert. No. 40036240
- UL E214025
- TÜV 968/EL908



Technical data of approved types on request

# SCHRACK SRL7

Force Guided Relay

## CONTACT DATA

Contact arrangement	5 form A + 2 form B contacts, (5 NO + 2 NC)
Rated voltage	250 VAC
Max. switching voltage	400 VAC
Rated current	6 A
Contact material	Ag alloy
Contact style	Single contact, force guided type A according to EN 50205
Min. recommended contact load	5V/10 mA
Initial contact resistance	≤100 mΩ at 1 A, 24 VDC ≤20 Ω at 10 mA, 5 VDC
Frequency of operation, with/without load	6/300 min <sup>-1</sup>
Mechanical endurance	10x10 <sup>6</sup> operations

## CONTACT RATINGS

Contact	Load	Cycles
<b>UL61810-1 (former UL508)</b>		
NO/NC	6 A, 250 VAC, general purpose, 85 °C	6.000
<b>IEC61810</b>		
NO/NC	6 A, 250 VAC, cosphi=1, 50% DF, 85 °C	6.000
NO (1 form A)	5 A, 24 VDC, DC-13	6.050
NO (1 form A)	3 A, 250 VAC, AC-15	6.050

## INSULATION DATA

	Group A	Group B
Initial dielectric strength		
between open contacts	1000 Vrms	1000 Vrms
between contact and coil	4000 Vrms	2500 Vrms
between adjacent contacts	4000 Vrms	2500 Vrms
between group A and group B	4000 Vrms	
Clearance/creepage		
between open contacts	microdisconnection	
between contact and coil	≥ 5.5/5.5 mm	≥ 3/4 mm
between adjacent contacts	≥ 5.5/5.5 mm	≥ 3/4 mm
between group A and group B	≥ 5.5/5.5 mm	

## COIL DATA

Coil voltage range	5 VDC to 110 VDC
Operative range, IEC 61810	2
Max. coil power	700 mW

## COIL VERSIONS, DC COIL

Coil code	Rated voltage VDC	Operate voltage VDC	Release voltage VDC	Coil resistance Ω±10%	Rated coil power mW
005	5	3.8	0.5	36	694
006	6	4.5	0.6	51	706
009	9	6.8	0.9	116	698
012	12	9	1.2	206	699
015	15	11.3	1.5	319	705
018	18	13.5	1.8	463	700
021	21	16	2.1	630	700
024	24	18	2.4	820	702
036	36	27	3.6	1850	701
048	48	36	4.8	3290	700
060	60	45	6	5140	700
110	110	83	11	17280	700

All figures are given for coil without pre-energization, at ambient temperature +23°C.

	Group A	Group B
Insulation to EN 62477 (former EN 50178), type of insulation		
between contact and coil	reinforced	basic
between adjacent contacts	reinforced	basic
between group A and group B	reinforced	

## OTHER DATA

Ambient temperature	-40 °C to +85 °C
Category of environmental protection	
IEC 61810	RTII
Packaging/unit	20 pcs. tray / 200 pcs. box

For more detailed information see product specification 2158004

# SCHRACK SRL7




Force Guided Relay

## DIMENSIONS (Unit:mm)

7 pole, 5 form A + 2 form B, 5NO + 2NC


Low cover

Normal cover



## PCB LAYOUT / TERMINAL ASSIGNMENT

Bottom view on solder pins



## PRODUCT CODE STRUCTURE

**Part Number**  
SRL 7 -5 2 3 -D 024 -0010

### Type

<b>SRL</b>	Relay with force guided contacts SRL
------------	--------------------------------------

### Version

<b>7</b>	7 pole
----------	--------

### Number of NO contact configurations

<b>5</b>	5 form A, NO sets
----------	-------------------

### Number of NC contact configurations

<b>2</b>	2 form B, NC sets
----------	-------------------

### Cover Version

<b>-0010</b>	Normal cover (11,5 mm height)
<b>blank</b>	Low cover (10,8 mm height)

### Coil

<b>Coil code</b>	please refer to coil versions table (e.g. 012=12 VDC)
------------------	---

### Coil system

<b>D</b>	DC Coil
----------	---------

### Contact material

<b>3</b>	AgSnO <sub>2</sub>
----------	--------------------

## PRODUCT INFORMATION

Product code	Type	Contact arrangement	Contact material	Coil	Part Number
SRL7-523-D012-0010	7 pole relay with force guided contacts	5 form A + 2 form B contacts (5 NO + 2 NC)	AgSnO <sub>2</sub>	12 VDC	<a href="#">2-2045880-4</a>
SRL7-523-D018-0010				18 VDC	<a href="#">2-2045880-6</a>
SRL7-523-D021-0010				21 VDC	<a href="#">2-2045880-7</a>
SRL7-523-D024-0010				24 VDC	<a href="#">2-2045880-8</a>

Note. This list represents the most common types and does not show all variants covered by this datasheet. Other types on request.

### Notes:

1. Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.
2. Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at <http://relays.te.com/definitions>.
3. Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.
4. For general information on Force-Guided-Relays and our portfolio, please visit <http://www.te.com/fgf>.
5. For more detailed product-specific-information (such as B10d values, switching times, etc) please contact our Product Information Center (<https://www.te.com/usa-en/customer-support/customer-service.html>) and ask for the product-specification.

## te.com

©2024 TE Connectivity. All Rights Reserved.

TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks owned or licensed by the TE Connectivity family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

10/24 ED