



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
05 ₅	REVISED	06/21/94	JAD

ELECTRICAL
Nominal Impedance (Ohms) <u>50</u>
Frequency Range (GHz) DC to <u>18</u>
Volt Rating (VRMS MAX) @ Sea Level <u>335</u>
VSWR <u>1.05 + .005 f(GH)</u>
Insertion Loss (dB MAX) <u>.03 √f(GH)</u>
RF Leakage (dB MIN) <u>-[60-f(GH)]</u>
Corona, 70,000 Ft (VRMS MIN) <u>250</u>
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level <u>1,000</u>
Contact Resistance (Milliohms MAX) Center Contact <u>2.0</u> Outer Contact <u>2.0</u> Cable to Housing <u>N/A</u>
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) <u>670</u>
I.R.(Megohms MIN) <u>10,000</u>

MECHANICAL
Interface Dimensions MIL-STD-348A, Fig. 310.2
Recommended Mating Torque <u>7-10 in-lbs</u>
Mating Characteristics: Insertion (MAX Lbs) <u>3.0</u> Withdrawal (MIN Oz) <u>1.0</u>
Force to Engage and Disengage (In-Lbs MAX) <u>2.0</u>
Center Contact Captivation Axial (Lbs) <u>6.0</u> Radial (In-Oz) <u>N/A</u>
Cable Retention Axial Force (Lbs) <u>N/A</u> Torque (In-Oz) <u>N/A</u>
Weight (Grams) <u>2.2</u>

ENVIRONMENTAL
Temperature Rating <u>-65°C to +125°C</u>
Vibration MIL-STD-202, Method 204, Condition D.
Shock MIL-STD-202, Method 213, Condition I.
Thermal Shock MIL-STD-202, Method 107, Condition B. Except High Temp
Moisture Resistance MIL-STD-202, Method 106
Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H
COMPONENT	MATERIAL
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± °	
These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of items without written permission.	

USE ASS'Y PROCEDURE	DATE <u>2-5-69</u>
NO. AP. <u>N/A</u>	CHECKED BY <u>PRB</u>
	DATE <u>2-5-69</u>
	APPD BY <u>DS</u>
	DATE <u>2-5-69</u>

GOLD PLATE PER MIL-G-45204	FINISH
N/A	
GOLD PLATE PER MIL-G-45204	
AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	
TITLE OSM 4 HOLE FLANGE MOUNT JACK RECEPTACLE STRAIGHT TERMINAL	
SIZE B	CODE IDENT NO. 26805
2052-1215-00	REV 05 ₅
SCALE 5 : 1	SHEET 1 OF 1